

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762977

Luminaire Tested: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P762977  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR2015309035-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2964.6 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P762977

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P762977

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	93															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	91															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	91	89	88															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	89	87	86															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	87	85	84															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	85	83	82															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	83	81	80															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1843633
5°	1663301
10°	933535
15°	474529
20°	200908
25°	92744
30°	49103
35°	26450
40°	14149
45°	8359
50°	4844
55°	2572
60°	1639
65°	1163
70°	479
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8359 cd/sqm



TEST NUMBER: P762977

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1201.4	40.5
10°-20°	1183.0	39.9
20°-30°	386.5	13.0
30°-40°	131.6	4.4
40°-50°	44.2	1.5
50°-60°	13.3	0.4
60°-70°	4.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2770.8	93.5
0°-40°	2902.4	97.9
0°-60°	2959.9	99.8
0°-90°	2964.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2964.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16874	
5°	15165	###
15°	4195	1183
25°	769	386
35°	198	132
45°	54	44
55°	14	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762977

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16873.7
0.5°	16873.7
1°	16852.6
1.5°	16810.6
2°	16733.9
2.5°	16631.8
3°	16487.5
3.5°	16286.2
4°	15987.2
4.5°	15623.6
5°	15165.3
5.5°	14562.7
6°	13945.2
6.5°	13237.5
7°	12544.8
7.5°	11733.4
8°	11009.2
8.5°	10280.5
9°	9607.3
9.5°	8989.8
10°	8414.3
12.5°	6041.8
15°	4195.1
17.5°	2740.7
20°	1727.9
22.5°	1119.4
25°	769.3
27.5°	540.9
30°	389.2
32.5°	279.5
35°	198.3
37.5°	138.2
40°	99.2
42.5°	72.1
45°	54.1
47.5°	42.1
50°	28.5
52.5°	18.0
55°	13.5
57.5°	10.5
60°	7.5
62.5°	6.0
65°	4.5



TEST NUMBER: P762977  
CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBCSSQMMS

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.0
70°		1.5

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)