

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763288

Luminaire Tested: LD6D25D010-EU6DR4020359035-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR4020359035-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2946.3 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763288
CATALOG NUMBER: LD6D25D010-EU6DR4020359035-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P763288

CATALOG NUMBER: LD6D25D010-EU6DR4020359035-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																																				
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																																				
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																																				
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																																				
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																																				
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																																				
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																																				
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																																				
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	749496
5°	745855
10°	704997
15°	599340
20°	408490
25°	170442
30°	53594
35°	24903
40°	13778
45°	6320
50°	3060
55°	1676
60°	874
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6320 cd/sqm



TEST NUMBER: P763288

CATALOG NUMBER: LD6D25D010-EU6DR4020359035-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	635.0	21.6
10°-20°	1422.5	48.3
20°-30°	712.1	24.2
30°-40°	130.5	4.4
40°-50°	36.0	1.2
50°-60°	8.4	0.3
60°-70°	1.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2769.6	94.0
0°-40°	2900.1	98.4
0°-60°	2944.6	99.9
0°-90°	2946.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2946.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6860	
5°	6800	635
15°	5298	1423
25°	1414	712
35°	187	131
45°	41	36
55°	9	8
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P763288

CATALOG NUMBER: LD6D25D010-EU6DR4020359035-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	6859.7
2.5°	6849.7
5°	6800.4
7.5°	6643.3
10°	6354.4
12.5°	5904.0
15°	5298.5
17.5°	4511.0
20°	3513.2
22.5°	2395.2
25°	1413.8
27.5°	747.4
30°	424.8
32.5°	274.5
35°	186.7
37.5°	133.4
40°	96.6
42.5°	66.1
45°	40.9
47.5°	26.1
50°	18.0
52.5°	12.8
55°	8.8
57.5°	5.6
60°	4.0
62.5°	2.4
65°	1.2
67.5°	0.8
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)