

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769036

Luminaire Tested: LD6D60D010-EU6DR5055659027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR5055659027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6997.5 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769036

CATALOG NUMBER: LD6D60D010-EU6DR5055659027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P769036
 CATALOG NUMBER: LD6D60D010-EU6DR5055659027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95																												
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																												
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																												
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																												
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76																												
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																												
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																												
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																												
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																												
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1231882
5°	1218974
10°	1198897
15°	1091696
20°	908417
25°	644841
30°	341310
35°	139092
40°	51661
45°	23641
50°	9689
55°	5067
60°	2491
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23641 cd/sqm



TEST NUMBER: P769036

CATALOG NUMBER: LD6D60D010-EU6DR5055659027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1050.5	15.0
10°-20°	2654.9	37.9
20°-30°	2384.8	34.1
30°-40°	746.7	10.7
40°-50°	130.7	1.9
50°-60°	26.1	0.4
60°-70°	4.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6090.1	87.0
0°-40°	6836.8	97.7
0°-60°	6993.6	99.9
0°-90°	6997.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6997.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11275	
5°	11114	###
15°	9651	2655
25°	5349	2385
35°	1043	747
45°	153	131
55°	27	26
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769036

CATALOG NUMBER: LD6D60D010-EU6DR5055659027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	11274.7
2.5°	11218.7
5°	11114.1
7.5°	10954.4
10°	10806.1
12.5°	10330.8
15°	9651.2
17.5°	8788.0
20°	7812.8
22.5°	6684.4
25°	5348.9
27.5°	3932.5
30°	2705.3
32.5°	1761.4
35°	1042.8
37.5°	598.9
40°	362.2
42.5°	235.7
45°	153.0
47.5°	93.2
50°	57.0
52.5°	39.0
55°	26.6
57.5°	18.1
60°	11.4
62.5°	6.7
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)