

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769114

Luminaire Tested: LD6D60D010-EU6DR5555659027-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769114  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR5555659027-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7032.7 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P769114  
CATALOG NUMBER: LD6D60D010-EU6DR5555659027-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P769114  
 CATALOG NUMBER: LD6D60D010-EU6DR5555659027-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57				
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54				
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	861630
5°	827412
10°	824286
15°	800606
20°	717857
25°	593280
30°	448145
35°	324947
40°	207954
45°	94982
50°	31055
55°	13411
60°	5769
65°	750
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 94982 cd/sqm



TEST NUMBER: P769114

CATALOG NUMBER: LD6D60D010-EU6DR5555659027-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	717.8	10.2
10°-20°	1959.1	27.9
20°-30°	2232.6	31.7
30°-40°	1519.9	21.6
40°-50°	523.7	7.4
50°-60°	72.4	1.0
60°-70°	7.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4909.6	69.8
0°-40°	6429.5	91.4
0°-60°	7025.7	99.9
0°-90°	7032.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7032.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7886	
5°	7544	718
15°	7078	1959
25°	4921	2233
35°	2436	1520
45°	615	524
55°	70	72
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769114

CATALOG NUMBER: LD6D60D010-EU6DR5555659027-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7886.0
2.5°	7705.2
5°	7544.0
7.5°	7464.8
10°	7429.6
12.5°	7312.4
15°	7077.8
17.5°	6705.5
20°	6173.9
22.5°	5560.3
25°	4921.2
27.5°	4255.7
30°	3552.1
32.5°	2956.0
35°	2436.2
37.5°	1941.7
40°	1458.0
42.5°	1010.4
45°	614.7
47.5°	331.3
50°	182.7
52.5°	108.5
55°	70.4
57.5°	45.0
60°	26.4
62.5°	11.7
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)