

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769227

Luminaire Tested: LD6D60D010-EU6DR6055659035-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6055659035-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5789.9 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769227

CATALOG NUMBER: LD6D60D010-EU6DR6055659035-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P769227

CATALOG NUMBER: LD6D60D010-EU6DR6055659035-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	751310
5°	769787
10°	779087
15°	742182
20°	654372
25°	529277
30°	358014
35°	179400
40°	29096
45°	28478
50°	29050
55°	29488
60°	30309
65°	30998
70°	31722
75°	32126
80°	30957
85°	25825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 32126 cd/sqm



TEST NUMBER: P769227

CATALOG NUMBER: LD6D60D010-EU6DR6055659035-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.8	11.6
10°-20°	1814.9	31.3
20°-30°	1952.7	33.7
30°-40°	848.8	14.7
40°-50°	142.5	2.5
50°-60°	138.6	2.4
60°-70°	118.6	2.0
70°-80°	79.3	1.4
80°-90°	23.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4438.4	76.7
0°-40°	5287.1	91.3
0°-60°	5568.3	96.2
0°-90°	5789.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5789.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6876	
5°	7019	671
15°	6561	1815
25°	4390	1953
35°	1345	849
45°	184	143
55°	155	139
65°	120	119
75°	76	79
85°	21	24
90°	0	



TEST NUMBER: P769227

CATALOG NUMBER: LD6D60D010-EU6DR6055659035-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6876.3
2.5°	7069.6
5°	7018.6
7.5°	7034.7
10°	7022.2
12.5°	6877.2
15°	6561.3
17.5°	6137.1
20°	5627.9
22.5°	5082.9
25°	4390.3
27.5°	3511.5
30°	2837.7
32.5°	2187.1
35°	1345.0
37.5°	575.4
40°	204.0
42.5°	187.9
45°	184.3
47.5°	178.1
50°	170.9
52.5°	162.9
55°	154.8
57.5°	146.8
60°	138.7
62.5°	129.8
65°	119.9
67.5°	110.1
70°	99.3
72.5°	87.7
75°	76.1
77.5°	62.6
80°	49.2
82.5°	34.9
85°	20.6
87.5°	7.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)