

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766942

Luminaire Tested: LD6D45BD010-EU6DR6540509030-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509030-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4315.1 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P766942
CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P766942

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228826
5°	228246
10°	228057
15°	221027
20°	201217
25°	175345
30°	145837
35°	115553
40°	83400
45°	52688
50°	27467
55°	14602
60°	7663
65°	4215
70°	1776
75°	1941
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52688 cd/sqm



TEST NUMBER: P766942

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	370.5	8.6
10°-20°	1014.6	23.5
20°-30°	1240.2	28.7
30°-40°	1006.3	23.3
40°-50°	501.4	11.6
50°-60°	139.9	3.2
60°-70°	31.8	0.7
70°-80°	8.3	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2625.4	60.8
0°-40°	3631.6	84.2
0°-60°	4272.9	99.0
0°-90°	4315.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4315.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3918	
5°	3893	371
15°	3656	1015
25°	2721	1240
35°	1621	1006
45°	638	501
55°	143	140
65°	30	32
75°	9	8
85°	2	2
90°	0	



TEST NUMBER: P766942

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3918.0
2.5°	3915.1
5°	3893.2
7.5°	3880.6
10°	3845.5
12.5°	3774.1
15°	3655.5
17.5°	3470.1
20°	3237.5
22.5°	2986.4
25°	2721.0
27.5°	2437.2
30°	2162.5
32.5°	1891.4
35°	1620.7
37.5°	1350.7
40°	1093.9
42.5°	853.3
45°	637.9
47.5°	444.5
50°	302.3
52.5°	208.4
55°	143.4
57.5°	96.7
60°	65.6
62.5°	45.5
65°	30.5
67.5°	15.5
70°	10.4
72.5°	9.8
75°	8.6
77.5°	5.8
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)