

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769153

Luminaire Tested: LD6D60D010-EU6DR5555659040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR5555659040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7663.8 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769153
CATALOG NUMBER: LD6D60D010-EU6DR5555659040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P769153

CATALOG NUMBER: LD6D60D010-EU6DR5555659040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94	94													
	2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87													
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81													
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75													
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70													
	6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65	65	65	65	65													
	7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61	61	61	61	61	61													
	8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57	57	57	57	57	57													
	9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54	54	54	54	54	54													
	10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	938954
5°	901664
10°	898265
15°	872456
20°	782284
25°	646517
30°	488366
35°	354105
40°	226610
45°	103496
50°	33843
55°	14611
60°	6293
65°	827
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 103496 cd/sqm



TEST NUMBER: P769153

CATALOG NUMBER: LD6D60D010-EU6DR5555659040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	782.3	10.2
10°-20°	2135.0	27.9
20°-30°	2433.0	31.7
30°-40°	1656.3	21.6
40°-50°	570.7	7.4
50°-60°	78.9	1.0
60°-70°	7.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5350.2	69.8
0°-40°	7006.5	91.4
0°-60°	7656.1	99.9
0°-90°	7663.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7663.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8594	
5°	8221	782
15°	7713	2135
25°	5363	2433
35°	2655	1656
45°	670	571
55°	77	79
65°	3	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769153

CATALOG NUMBER: LD6D60D010-EU6DR5555659040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8593.7
2.5°	8396.7
5°	8221.0
7.5°	8134.7
10°	8096.4
12.5°	7968.6
15°	7713.0
17.5°	7307.3
20°	6728.0
22.5°	6059.3
25°	5362.8
27.5°	4637.6
30°	3870.9
32.5°	3221.3
35°	2654.8
37.5°	2115.9
40°	1588.8
42.5°	1101.1
45°	669.8
47.5°	361.0
50°	199.1
52.5°	118.2
55°	76.7
57.5°	49.0
60°	28.8
62.5°	12.8
65°	3.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)