

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767044

Luminaire Tested: LD6D45BD010-EU6DR7040509035-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR7040509035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4115.1 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767044

CATALOG NUMBER: LD6D45BD010-EU6DR7040509035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P767044

CATALOG NUMBER: LD6D45BD010-EU6DR7040509035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	505495
5°	490470
10°	476803
15°	470547
20°	439395
25°	330094
30°	233352
35°	82657
40°	43459
45°	46294
50°	47934
55°	48842
60°	49145
65°	48113
70°	45395
75°	42046
80°	37312
85°	30338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 49150 cd/sqm



TEST NUMBER: P767044

CATALOG NUMBER: LD6D45BD010-EU6DR7040509035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	421.8	10.3
10°-20°	1157.0	28.1
20°-30°	1274.3	31.0
30°-40°	486.9	11.8
40°-50°	229.9	5.6
50°-60°	228.5	5.6
60°-70°	183.0	4.4
70°-80°	105.2	2.6
80°-90°	28.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2853.0	69.3
0°-40°	3339.9	81.2
0°-60°	3798.3	92.3
0°-90°	4115.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4115.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4626	
5°	4472	422
15°	4160	1157
25°	2738	1274
35°	620	487
45°	300	230
55°	256	229
65°	186	183
75°	100	105
85°	24	29
90°	0	



TEST NUMBER: P767044

CATALOG NUMBER: LD6D45BD010-EU6DR7040509035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4626.5
2.5°	4578.1
5°	4471.9
7.5°	4383.3
10°	4297.6
12.5°	4225.1
15°	4159.9
17.5°	4002.4
20°	3779.0
22.5°	3297.0
25°	2738.1
27.5°	2383.6
30°	1849.6
32.5°	1194.7
35°	619.7
37.5°	334.8
40°	304.7
42.5°	302.5
45°	299.6
47.5°	293.0
50°	282.0
52.5°	269.6
55°	256.4
57.5°	241.7
60°	224.9
62.5°	205.8
65°	186.1
67.5°	164.1
70°	142.1
72.5°	120.1
75°	99.6
77.5°	78.4
80°	59.3
82.5°	41.8
85°	24.2
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)