

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768786

Luminaire Tested: LD6D60D010-EU6DR3055659050-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR3055659050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6262.4 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768786

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768786

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1541324	1541324	1541324
5°	1497076	1495332	1497153
10°	1296696	1287548	1296385
15°	846028	841487	837256
20°	420687	436473	420124
25°	211918	238969	207577
30°	84849	92450	73925
35°	39358	37695	31593
40°	16986	18865	16007
45°	11983	14873	12091
50°	4120	10836	4358
55°	2375	4484	2509
60°	1669	1975	1669
65°	1069	1069	1069
70°	671	448	671
75°	0	296	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 14873 cd/sqm



TEST NUMBER: P768786

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1770.7	28.3
10°-20°	2851.7	45.5
20°-30°	1232.3	19.7
30°-40°	280.9	4.5
40°-50°	96.4	1.5
50°-60°	23.6	0.4
60°-70°	6.1	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5854.8	93.5
0°-40°	6135.6	98.0
0°-60°	6255.6	99.9
0°-90°	6262.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6262.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20137	20137	20137	20137	20137	
5°	19484	19465	19461	19502	19485	1772
15°	10676	10548	10619	10584	10566	2859
25°	2509	2604	2830	2538	2458	1201
35°	421	430	403	400	338	286
45°	111	137	137	137	112	79
55°	18	19	34	20	19	17
65°	6	6	6	6	6	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768786

CATALOG NUMBER: LD6D60D010-EU6DR3055659050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20136.6	20136.6	20136.6	20136.6	20136.6
2.5°	20003.1	19989.3	19997.2	20007.1	20011.0
5°	19484.1	19465.3	19461.4	19501.9	19485.1
7.5°	18437.1	18410.4	18369.9	18461.8	18547.9
10°	16683.3	16653.6	16565.6	16609.1	16679.3
12.5°	14094.0	13998.1	13996.2	14134.6	14115.8
15°	10676.3	10547.8	10619.0	10584.4	10565.6
17.5°	7179.5	7130.1	7225.0	7196.3	7072.7
20°	5164.6	5177.5	5358.4	5267.5	5157.7
22.5°	3768.7	3815.2	4029.7	3795.4	3709.4
25°	2509.2	2604.1	2829.5	2537.8	2457.8
27.5°	1543.3	1586.8	1815.1	1523.5	1480.0
30°	960.0	938.2	1046.0	897.7	836.4
32.5°	629.8	602.1	636.7	571.4	522.0
35°	421.2	430.1	403.4	400.4	338.1
37.5°	263.0	302.5	266.9	284.7	217.5
40°	170.0	219.5	188.8	208.6	160.2
42.5°	139.4	169.1	155.2	165.1	142.4
45°	110.7	137.4	137.4	137.4	111.7
47.5°	61.3	91.9	117.6	93.9	65.3
50°	34.6	46.5	91.0	48.4	36.6
52.5°	23.7	26.7	62.3	27.7	24.7
55°	17.8	18.8	33.6	19.8	18.8
57.5°	13.8	14.8	17.8	14.8	13.8
60°	10.9	10.9	12.9	11.9	10.9
62.5°	7.9	7.9	8.9	7.9	7.9
65°	5.9	5.9	5.9	5.9	5.9
67.5°	3.0	4.0	4.0	4.0	4.0
70°	3.0	2.0	2.0	2.0	3.0
72.5°	2.0	1.0	1.0	1.0	1.0
75°	0.0	0.0	1.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)