

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766967

Luminaire Tested: LD6D45BD010-EU6DR6540509040-6LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P766967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR6540509040-6LBCSSQMB  
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4564.4 lumens  
Efficiency: N/A  
Efficacy: 117.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P766967

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P766967

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	242049
5°	241438
10°	241228
15°	233797
20°	212840
25°	185476
30°	154267
35°	122233
40°	88218
45°	55735
50°	29048
55°	15437
60°	8106
65°	4464
70°	1878
75°	2053
80°	1446
85°	1206

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 55735 cd/sqm



TEST NUMBER: P766967

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	391.9	8.6
10°-20°	1073.2	23.5
20°-30°	1311.9	28.7
30°-40°	1064.4	23.3
40°-50°	530.4	11.6
50°-60°	147.9	3.2
60°-70°	33.6	0.7
70°-80°	8.8	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2777.0	60.8
0°-40°	3841.5	84.2
0°-60°	4519.8	99.0
0°-90°	4564.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4564.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4144	
5°	4118	392
15°	3867	1073
25°	2878	1312
35°	1714	1064
45°	675	530
55°	152	148
65°	32	34
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P766967

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4144.4
2.5°	4141.3
5°	4118.2
7.5°	4104.8
10°	4067.6
12.5°	3992.1
15°	3866.7
17.5°	3670.6
20°	3424.5
22.5°	3159.0
25°	2878.2
27.5°	2578.0
30°	2287.5
32.5°	2000.6
35°	1714.4
37.5°	1428.8
40°	1157.1
42.5°	902.6
45°	674.8
47.5°	470.2
50°	319.7
52.5°	220.5
55°	151.6
57.5°	102.3
60°	69.4
62.5°	48.1
65°	32.3
67.5°	16.4
70°	11.0
72.5°	10.4
75°	9.1
77.5°	6.1
80°	4.3
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)