

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767057

Luminaire Tested: LD6D45BD010-EU6DR7040509040-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P767057  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR7040509040-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4307.4 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P767057  
CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P767057

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	529128
5°	513403
10°	499092
15°	492548
20°	459929
25°	345525
30°	244252
35°	86525
40°	45499
45°	48457
50°	50178
55°	51128
60°	51440
65°	50362
70°	47503
75°	44030
80°	39074
85°	31717

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 51448 cd/sqm



TEST NUMBER: P767057

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	441.5	10.3
10°-20°	1211.1	28.1
20°-30°	1333.8	31.0
30°-40°	509.6	11.8
40°-50°	240.6	5.6
50°-60°	239.2	5.6
60°-70°	191.6	4.4
70°-80°	110.1	2.6
80°-90°	29.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2986.4	69.3
0°-40°	3496.0	81.2
0°-60°	3975.9	92.3
0°-90°	4307.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4307.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4843	
5°	4681	442
15°	4354	1211
25°	2866	1334
35°	649	510
45°	314	241
55°	268	239
65°	195	192
75°	104	110
85°	25	30
90°	0	



TEST NUMBER: P767057

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4842.8
2.5°	4792.2
5°	4681.0
7.5°	4588.2
10°	4498.5
12.5°	4422.6
15°	4354.4
17.5°	4189.5
20°	3955.6
22.5°	3451.1
25°	2866.1
27.5°	2495.0
30°	1936.0
32.5°	1250.6
35°	648.7
37.5°	350.4
40°	319.0
42.5°	316.7
45°	313.6
47.5°	306.7
50°	295.2
52.5°	282.2
55°	268.4
57.5°	253.0
60°	235.4
62.5°	215.5
65°	194.8
67.5°	171.8
70°	148.7
72.5°	125.7
75°	104.3
77.5°	82.0
80°	62.1
82.5°	43.7
85°	25.3
87.5°	10.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)