

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769515

Luminaire Tested: LD6D65D010-EU6DR3055659030-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR3055659030-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7061.5 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769515
CATALOG NUMBER: LD6D65D010-EU6DR3055659030-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P769515

CATALOG NUMBER: LD6D65D010-EU6DR3055659030-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738017	1738017	1738017
5°	1688120	1686153	1688205
10°	1462171	1451857	1461821
15°	953989	948870	944100
20°	474374	492172	473739
25°	238961	269466	234062
30°	95676	104250	83356
35°	44376	42498	35630
40°	19155	21273	18046
45°	13520	16779	13639
50°	4644	12218	4906
55°	2682	5058	2829
60°	1883	2220	1883
65°	1213	1213	1213
70°	739	492	739
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16779 cd/sqm



TEST NUMBER: P769515
 CATALOG NUMBER: LD6D65D010-EU6DR3055659030-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1996.7	28.3
10°-20°	3215.7	45.5
20°-30°	1389.6	19.7
30°-40°	316.7	4.5
40°-50°	108.8	1.5
50°-60°	26.6	0.4
60°-70°	6.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6601.9	93.5
0°-40°	6918.6	98.0
0°-60°	7053.9	99.9
0°-90°	7061.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7061.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	22706	22706	22706	22706	22706	
5°	21970	21949	21945	21991	21972	1998
15°	12039	11894	11974	11935	11914	3224
25°	2829	2936	3191	2862	2771	1354
35°	475	485	455	452	381	322
45°	125	155	155	155	126	89
55°	20	21	38	22	21	20
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P769515

CATALOG NUMBER: LD6D65D010-EU6DR3055659030-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	22706.3	22706.3	22706.3	22706.3	22706.3
2.5°	22555.8	22540.2	22549.1	22560.2	22564.7
5°	21970.5	21949.3	21944.9	21990.6	21971.6
7.5°	20789.9	20759.8	20714.1	20817.8	20914.8
10°	18812.3	18778.8	18679.6	18728.7	18807.8
12.5°	15892.6	15784.5	15782.2	15938.3	15917.1
15°	12038.7	11893.8	11974.1	11935.1	11913.9
17.5°	8095.7	8040.0	8147.0	8114.6	7975.3
20°	5823.7	5838.2	6042.2	5939.7	5815.9
22.5°	4249.6	4302.0	4543.9	4279.7	4182.7
25°	2829.4	2936.4	3190.6	2861.7	2771.4
27.5°	1740.2	1789.3	2046.8	1717.9	1668.9
30°	1082.5	1057.9	1179.5	1012.2	943.1
32.5°	710.1	678.9	717.9	644.4	588.6
35°	474.9	484.9	454.8	451.5	381.3
37.5°	296.5	341.1	301.0	321.1	245.3
40°	191.7	247.5	212.9	235.2	180.6
42.5°	157.2	190.6	175.0	186.2	160.5
45°	124.9	155.0	155.0	155.0	126.0
47.5°	69.1	103.7	132.7	105.9	73.6
50°	39.0	52.4	102.6	54.6	41.2
52.5°	26.8	30.1	70.2	31.2	27.9
55°	20.1	21.2	37.9	22.3	21.2
57.5°	15.6	16.7	20.1	16.7	15.6
60°	12.3	12.3	14.5	13.4	12.3
62.5°	8.9	8.9	10.0	8.9	8.9
65°	6.7	6.7	6.7	6.7	6.7
67.5°	3.3	4.5	4.5	4.5	4.5
70°	3.3	2.2	2.2	2.2	3.3
72.5°	2.2	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)