

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766825

Luminaire Tested: LD6D45BD010-EU6DR5540509050-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR5540509050-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5250.4 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P766825

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P766825

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																												
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																												
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75																												
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70																												
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65																												
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61																												
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57																												
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54																												
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	643273
5°	617729
10°	615397
15°	597723
20°	535937
25°	442922
30°	334573
35°	242597
40°	155253
45°	70908
50°	23185
55°	10001
60°	4305
65°	569
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 70908 cd/sqm



TEST NUMBER: P766825

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.9	10.2
10°-20°	1462.7	27.9
20°-30°	1666.8	31.7
30°-40°	1134.7	21.6
40°-50°	391.0	7.4
50°-60°	54.1	1.0
60°-70°	5.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3665.4	69.8
0°-40°	4800.1	91.4
0°-60°	5245.2	99.9
0°-90°	5250.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5250.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5888	
5°	5632	536
15°	5284	1463
25°	3674	1667
35°	1819	1135
45°	459	391
55°	52	54
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P766825
CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5887.5
2.5°	5752.5
5°	5632.2
7.5°	5573.1
10°	5546.8
12.5°	5459.2
15°	5284.2
17.5°	5006.2
20°	4609.3
22.5°	4151.2
25°	3674.0
27.5°	3177.2
30°	2651.9
32.5°	2206.9
35°	1818.8
37.5°	1449.6
40°	1088.5
42.5°	754.4
45°	458.9
47.5°	247.3
50°	136.4
52.5°	81.0
55°	52.5
57.5°	33.6
60°	19.7
62.5°	8.8
65°	2.2
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)