

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770063

Luminaire Tested: LD6D65D010-EU6DR6555659030-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659030-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7098.2 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770063
CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P770063

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376413
5°	375465
10°	375145
15°	363577
20°	330991
25°	288440
30°	239901
35°	190087
40°	137195
45°	86676
50°	45176
55°	24010
60°	12615
65°	6937
70°	2903
75°	3204
80°	2220
85°	1876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 86676 cd/sqm



TEST NUMBER: P770063

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.5	8.6
10°-20°	1669.0	23.5
20°-30°	2040.1	28.7
30°-40°	1655.3	23.3
40°-50°	824.9	11.6
50°-60°	230.1	3.2
60°-70°	52.3	0.7
70°-80°	13.6	0.2
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4318.6	60.8
0°-40°	5973.9	84.2
0°-60°	7028.9	99.0
0°-90°	7098.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7098.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6445	
5°	6404	609
15°	6013	1669
25°	4476	2040
35°	2666	1655
45°	1049	825
55°	236	230
65°	50	52
75°	14	14
85°	3	3
90°	0	



TEST NUMBER: P770063

CATALOG NUMBER: LD6D65D010-EU6DR6555659030-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6445.0
2.5°	6440.3
5°	6404.3
7.5°	6383.4
10°	6325.7
12.5°	6208.2
15°	6013.1
17.5°	5708.2
20°	5325.5
22.5°	4912.6
25°	4476.0
27.5°	4009.1
30°	3557.3
32.5°	3111.2
35°	2666.1
37.5°	2221.9
40°	1799.5
42.5°	1403.6
45°	1049.4
47.5°	731.2
50°	497.2
52.5°	342.8
55°	235.8
57.5°	159.1
60°	108.0
62.5°	74.8
65°	50.2
67.5°	25.6
70°	17.0
72.5°	16.1
75°	14.2
77.5°	9.5
80°	6.6
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)