

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758768

Luminaire Tested: LD6D05D010-EU6DR700210IC9024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P758768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR700210IC9024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 359.5 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758768

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P758768

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44163
5°	42840
10°	41649
15°	41106
20°	38382
25°	28837
30°	20388
35°	7216
40°	3794
45°	4048
50°	4181
55°	4267
60°	4305
65°	4214
70°	3961
75°	3673
80°	3272
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 4305 cd/sqm



TEST NUMBER: P758768

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.8	10.2
10°-20°	101.1	28.1
20°-30°	111.3	31.0
30°-40°	42.5	11.8
40°-50°	20.1	5.6
50°-60°	20.0	5.6
60°-70°	16.0	4.5
70°-80°	9.2	2.6
80°-90°	2.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.2	69.3
0°-40°	291.7	81.2
0°-60°	331.8	92.3
0°-90°	359.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	391	37
15°	363	101
25°	239	111
35°	54	43
45°	26	20
55°	22	20
65°	16	16
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P758768

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	404.2
2.5°	399.9
5°	390.6
7.5°	382.9
10°	375.4
12.5°	369.1
15°	363.4
17.5°	349.6
20°	330.1
22.5°	288.0
25°	239.2
27.5°	208.2
30°	161.6
32.5°	104.4
35°	54.1
37.5°	29.2
40°	26.6
42.5°	26.4
45°	26.2
47.5°	25.6
50°	24.6
52.5°	23.5
55°	22.4
57.5°	21.1
60°	19.7
62.5°	18.0
65°	16.3
67.5°	14.3
70°	12.4
72.5°	10.5
75°	8.7
77.5°	6.8
80°	5.2
82.5°	3.7
85°	2.1
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)