

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769566

Luminaire Tested: LD6D65D010-EU6DR3055659050-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR3055659050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6926.1 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769566

CATALOG NUMBER: LD6D65D010-EU6DR3055659050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P769566

CATALOG NUMBER: LD6D65D010-EU6DR3055659050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1704675	1704675	1704675
5°	1655742	1653806	1655826
10°	1434120	1424008	1433778
15°	935692	930668	925993
20°	465275	482731	464656
25°	234375	264298	229569
30°	93838	102243	81756
35°	43525	41685	34938
40°	18795	20863	17696
45°	13260	16454	13380
50°	4561	11979	4823
55°	2629	4964	2776
60°	1837	2174	1837
65°	1195	1195	1195
70°	739	492	739
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16454 cd/sqm



TEST NUMBER: P769566

CATALOG NUMBER: LD6D65D010-EU6DR3055659050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1958.4	28.3
10°-20°	3154.0	45.5
20°-30°	1362.9	19.7
30°-40°	310.6	4.5
40°-50°	106.7	1.5
50°-60°	26.1	0.4
60°-70°	6.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6475.3	93.5
0°-40°	6785.9	98.0
0°-60°	6918.6	99.9
0°-90°	6926.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6926.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	22271	22271	22271	22271	22271	
5°	21549	21528	21524	21569	21550	1960
15°	11808	11666	11744	11706	11685	3162
25°	2775	2880	3129	2807	2718	1328
35°	466	476	446	443	374	316
45°	122	152	152	152	124	87
55°	20	21	37	22	21	19
65°	7	7	7	7	7	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P769566

CATALOG NUMBER: LD6D65D010-EU6DR3055659050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	22270.7	22270.7	22270.7	22270.7	22270.7
2.5°	22123.1	22107.8	22116.6	22127.5	22131.9
5°	21549.1	21528.3	21523.9	21568.8	21550.2
7.5°	20391.1	20361.6	20316.8	20418.5	20513.6
10°	18451.4	18418.6	18321.3	18369.4	18447.0
12.5°	15587.8	15481.7	15479.5	15632.6	15611.8
15°	11807.8	11665.7	11744.4	11706.1	11685.4
17.5°	7940.4	7885.7	7990.7	7959.0	7822.3
20°	5712.0	5726.2	5926.3	5825.7	5704.4
22.5°	4168.1	4219.5	4456.8	4197.6	4102.5
25°	2775.1	2880.1	3129.4	2806.8	2718.2
27.5°	1706.8	1754.9	2007.5	1685.0	1636.8
30°	1061.7	1037.7	1156.8	992.8	925.0
32.5°	696.5	665.9	704.2	632.0	577.3
35°	465.8	475.6	446.1	442.8	373.9
37.5°	290.8	334.6	295.2	314.9	240.6
40°	188.1	242.7	208.8	230.7	177.1
42.5°	154.2	187.0	171.7	182.6	157.5
45°	122.5	152.0	152.0	152.0	123.6
47.5°	67.8	101.7	130.1	103.9	72.2
50°	38.3	51.4	100.6	53.6	40.5
52.5°	26.2	29.5	68.9	30.6	27.3
55°	19.7	20.8	37.2	21.9	20.8
57.5°	15.3	16.4	19.7	16.4	15.3
60°	12.0	12.0	14.2	13.1	12.0
62.5°	8.7	8.7	9.8	8.7	8.7
65°	6.6	6.6	6.6	6.6	6.6
67.5°	3.3	4.4	4.4	4.4	4.4
70°	3.3	2.2	2.2	2.2	3.3
72.5°	2.2	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)