

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758769

Luminaire Tested: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P758769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 478.8 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P758769
CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P758769

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58804
5°	57066
10°	55473
15°	54748
20°	51114
25°	38409
30°	27150
35°	9617
40°	5063
45°	5377
50°	5575
55°	5696
60°	5725
65°	5610
70°	5303
75°	4897
80°	4342
85°	3510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 5725 cd/sqm



TEST NUMBER: P758769

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	10.2
10°-20°	134.6	28.1
20°-30°	148.3	31.0
30°-40°	56.7	11.8
40°-50°	26.7	5.6
50°-60°	26.6	5.6
60°-70°	21.3	4.4
70°-80°	12.2	2.6
80°-90°	3.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.9	69.3
0°-40°	388.6	81.2
0°-60°	441.9	92.3
0°-90°	478.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	538	
5°	520	49
15°	484	135
25°	319	148
35°	72	57
45°	35	27
55°	30	27
65°	22	21
75°	12	12
85°	3	3
90°	0	



TEST NUMBER: P758769

CATALOG NUMBER: LD6D05D010-EU6DR700210IC9024-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	538.2
2.5°	532.6
5°	520.3
7.5°	510.0
10°	500.0
12.5°	491.5
15°	484.0
17.5°	465.6
20°	439.6
22.5°	383.6
25°	318.6
27.5°	277.3
30°	215.2
32.5°	139.0
35°	72.1
37.5°	39.0
40°	35.5
42.5°	35.2
45°	34.8
47.5°	34.1
50°	32.8
52.5°	31.3
55°	29.9
57.5°	28.1
60°	26.2
62.5°	23.9
65°	21.7
67.5°	19.1
70°	16.6
72.5°	14.0
75°	11.6
77.5°	9.1
80°	6.9
82.5°	4.9
85°	2.8
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)