

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767658

Luminaire Tested: LD6D50D010-EU6DR6040509035-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6040509035-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5725.5 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767658

CATALOG NUMBER: LD6D50D010-EU6DR6040509035-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P767658
 CATALOG NUMBER: LD6D50D010-EU6DR6040509035-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																												
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																												
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75																												
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70																												
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65																												
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61																												
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57																												
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																												
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	626042
5°	624507
10°	645252
15°	645921
20°	594317
25°	505503
30°	385177
35°	272381
40°	159945
45°	64542
50°	21553
55°	10363
60°	4261
65°	620
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 64542 cd/sqm



TEST NUMBER: P767658

CATALOG NUMBER: LD6D50D010-EU6DR6040509035-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.3	9.6
10°-20°	1581.9	27.6
20°-30°	1893.4	33.1
30°-40°	1266.4	22.1
40°-50°	375.5	6.6
50°-60°	54.0	0.9
60°-70°	5.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4024.6	70.3
0°-40°	5291.0	92.4
0°-60°	5720.4	99.9
0°-90°	5725.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5725.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5730	
5°	5694	549
15°	5710	1582
25°	4193	1893
35°	2042	1266
45°	418	375
55°	54	54
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P767658

CATALOG NUMBER: LD6D50D010-EU6DR6040509035-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5729.8
2.5°	5722.5
5°	5694.0
7.5°	5771.2
10°	5815.9
12.5°	5807.8
15°	5710.3
17.5°	5480.3
20°	5111.4
22.5°	4668.5
25°	4193.1
27.5°	3657.6
30°	3053.0
32.5°	2513.4
35°	2042.1
37.5°	1570.0
40°	1121.4
42.5°	739.5
45°	417.7
47.5°	213.7
50°	126.8
52.5°	82.1
55°	54.4
57.5°	34.9
60°	19.5
62.5°	8.1
65°	2.4
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)