

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770762

Luminaire Tested: LD6D70BD010-EU6DR6070959027-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR6070959027-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7062.7 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P770762  
CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P770762

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	916468
5°	938998
10°	950344
15°	905328
20°	798225
25°	645625
30°	436715
35°	218841
40°	35501
45°	34751
50°	35441
55°	35965
60°	36974
65°	37823
70°	38718
75°	39176
80°	37752
85°	31466

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 39176 cd/sqm



TEST NUMBER: P770762

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	818.3	11.6
10°-20°	2213.8	31.3
20°-30°	2381.9	33.7
30°-40°	1035.4	14.7
40°-50°	173.9	2.5
50°-60°	169.1	2.4
60°-70°	144.6	2.0
70°-80°	96.8	1.4
80°-90°	28.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5414.0	76.7
0°-40°	6449.4	91.3
0°-60°	6792.4	96.2
0°-90°	7062.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7062.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8388	
5°	8561	818
15°	8004	2214
25°	5355	2382
35°	1641	1035
45°	225	174
55°	189	169
65°	146	145
75°	93	97
85°	25	29
90°	0	



TEST NUMBER: P770762

CATALOG NUMBER: LD6D70BD010-EU6DR6070959027-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8387.9
2.5°	8623.7
5°	8561.4
7.5°	8581.1
10°	8565.8
12.5°	8389.0
15°	8003.6
17.5°	7486.2
20°	6865.1
22.5°	6200.3
25°	5355.4
27.5°	4283.5
30°	3461.5
32.5°	2667.9
35°	1640.7
37.5°	701.9
40°	248.9
42.5°	229.2
45°	224.9
47.5°	217.2
50°	208.5
52.5°	198.7
55°	188.8
57.5°	179.0
60°	169.2
62.5°	158.3
65°	146.3
67.5°	134.3
70°	121.2
72.5°	107.0
75°	92.8
77.5°	76.4
80°	60.0
82.5°	42.6
85°	25.1
87.5°	8.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)