

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767824

Luminaire Tested: LD6D50D010-EU6DR7040509035-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR7040509035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4832.7 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767824

CATALOG NUMBER: LD6D50D010-EU6DR7040509035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P767824

CATALOG NUMBER: LD6D50D010-EU6DR7040509035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	593657
5°	576018
10°	559957
15°	552612
20°	516031
25°	387660
30°	274040
35°	97076
40°	51047
45°	54359
50°	56297
55°	57357
60°	57712
65°	56489
70°	53317
75°	49392
80°	43856
85°	35603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 57732 cd/sqm



TEST NUMBER: P767824

CATALOG NUMBER: LD6D50D010-EU6DR7040509035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	495.4	10.3
10°-20°	1358.8	28.1
20°-30°	1496.5	31.0
30°-40°	571.8	11.8
40°-50°	270.0	5.6
50°-60°	268.4	5.6
60°-70°	214.9	4.4
70°-80°	123.5	2.6
80°-90°	33.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3350.6	69.3
0°-40°	3922.4	81.2
0°-60°	4460.8	92.3
0°-90°	4832.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4832.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5433	
5°	5252	495
15°	4885	1359
25°	3216	1496
35°	728	572
45°	352	270
55°	301	268
65°	218	215
75°	117	124
85°	28	34
90°	0	



TEST NUMBER: P767824

CATALOG NUMBER: LD6D50D010-EU6DR7040509035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5433.4
2.5°	5376.6
5°	5251.9
7.5°	5147.8
10°	5047.1
12.5°	4961.9
15°	4885.4
17.5°	4700.4
20°	4438.1
22.5°	3872.0
25°	3215.6
27.5°	2799.3
30°	2172.1
32.5°	1403.1
35°	727.8
37.5°	393.1
40°	357.9
42.5°	355.3
45°	351.8
47.5°	344.1
50°	331.2
52.5°	316.6
55°	301.1
57.5°	283.9
60°	264.1
62.5°	241.7
65°	218.5
67.5°	192.7
70°	166.9
72.5°	141.1
75°	117.0
77.5°	92.0
80°	69.7
82.5°	49.0
85°	28.4
87.5°	11.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)