

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770839

Luminaire Tested: LD6D70BD010-EU6DR6570959027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5253.6 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770839
CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P770839

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565151
5°	565621
10°	585541
15°	586502
20°	539971
25°	460090
30°	352211
35°	248839
40°	146880
45°	59629
50°	21621
55°	12039
60°	6905
65°	3800
70°	3993
75°	3124
80°	3209
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59629 cd/sqm



TEST NUMBER: P770839

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	498.1	9.5
10°-20°	1436.7	27.3
20°-30°	1723.8	32.8
30°-40°	1158.4	22.1
40°-50°	346.8	6.6
50°-60°	61.2	1.2
60°-70°	17.4	0.3
70°-80°	8.5	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3658.6	69.6
0°-40°	4817.0	91.7
0°-60°	5225.0	99.5
0°-90°	5253.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5253.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5172	
5°	5157	498
15°	5185	1437
25°	3816	1724
35°	1866	1158
45°	386	347
55°	63	61
65°	15	17
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P770839

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5172.5
2.5°	5194.6
5°	5157.1
7.5°	5235.0
10°	5277.7
12.5°	5267.4
15°	5185.0
17.5°	4983.6
20°	4644.0
22.5°	4244.2
25°	3816.4
27.5°	3333.4
30°	2791.7
32.5°	2300.7
35°	1865.6
37.5°	1435.6
40°	1029.8
42.5°	672.6
45°	385.9
47.5°	204.3
50°	127.2
52.5°	88.2
55°	63.2
57.5°	45.6
60°	31.6
62.5°	20.6
65°	14.7
67.5°	13.2
70°	12.5
72.5°	9.6
75°	7.4
77.5°	6.6
80°	5.1
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)