

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767758

Luminaire Tested: LD6D50D010-EU6DR6540509040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6540509040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4084.7 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767758

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P767758

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439414
5°	439776
10°	455257
15°	456012
20°	419838
25°	357726
30°	273850
35°	193472
40°	114204
45°	46355
50°	16811
55°	9353
60°	5376
65°	2947
70°	3099
75°	2406
80°	2517
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46355 cd/sqm



TEST NUMBER: P767758

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	9.5
10°-20°	1117.1	27.3
20°-30°	1340.3	32.8
30°-40°	900.7	22.1
40°-50°	269.6	6.6
50°-60°	47.6	1.2
60°-70°	13.5	0.3
70°-80°	6.6	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2844.6	69.6
0°-40°	3745.3	91.7
0°-60°	4062.5	99.5
0°-90°	4084.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4084.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4022	
5°	4010	387
15°	4031	1117
25°	2967	1340
35°	1450	901
45°	300	270
55°	49	48
65°	11	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P767758

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4021.7
2.5°	4038.8
5°	4009.7
7.5°	4070.3
10°	4103.4
12.5°	4095.4
15°	4031.4
17.5°	3874.8
20°	3610.8
22.5°	3299.9
25°	2967.3
27.5°	2591.8
30°	2170.6
32.5°	1788.8
35°	1450.5
37.5°	1116.2
40°	800.7
42.5°	522.9
45°	300.0
47.5°	158.9
50°	98.9
52.5°	68.6
55°	49.1
57.5°	35.4
60°	24.6
62.5°	16.0
65°	11.4
67.5°	10.3
70°	9.7
72.5°	7.4
75°	5.7
77.5°	5.1
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)