

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770774

Luminaire Tested: LD6D70BD010-EU6DR6070959030-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770774  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR6070959030-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6459.3 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P770774  
CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P770774

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	838161
5°	858769
10°	869142
15°	827980
20°	730019
25°	590459
30°	399396
35°	200141
40°	32463
45°	31784
50°	32415
55°	32898
60°	33805
65°	34592
70°	35396
75°	35841
80°	34543
85°	28833

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 35841 cd/sqm



TEST NUMBER: P770774

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	748.3	11.6
10°-20°	2024.7	31.3
20°-30°	2178.4	33.7
30°-40°	946.9	14.7
40°-50°	159.1	2.5
50°-60°	154.6	2.4
60°-70°	132.3	2.0
70°-80°	88.5	1.4
80°-90°	26.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4951.4	76.7
0°-40°	5898.3	91.3
0°-60°	6212.0	96.2
0°-90°	6459.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6459.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7671	
5°	7830	748
15°	7320	2025
25°	4898	2178
35°	1500	947
45°	206	159
55°	173	155
65°	134	132
75°	85	89
85°	23	26
90°	0	



TEST NUMBER: P770774

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7671.2
2.5°	7886.8
5°	7829.9
7.5°	7847.9
10°	7833.9
12.5°	7672.2
15°	7319.8
17.5°	6846.6
20°	6278.5
22.5°	5670.5
25°	4897.8
27.5°	3917.5
30°	3165.7
32.5°	2439.9
35°	1500.5
37.5°	641.9
40°	227.6
42.5°	209.7
45°	205.7
47.5°	198.7
50°	190.7
52.5°	181.7
55°	172.7
57.5°	163.7
60°	154.7
62.5°	144.8
65°	133.8
67.5°	122.8
70°	110.8
72.5°	97.8
75°	84.9
77.5°	69.9
80°	54.9
82.5°	38.9
85°	23.0
87.5°	8.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)