

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770931

Luminaire Tested: LD6D70BD010-EU6DR7070959030-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770931
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959030-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6702.9 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770931
CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770931

CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	823389
5°	798917
10°	776646
15°	766456
20°	715718
25°	537679
30°	380093
35°	134637
40°	70801
45°	75405
50°	78089
55°	79549
60°	80044
65°	78361
70°	73954
75°	68515
80°	60781
85°	49393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 80060 cd/sqm



TEST NUMBER: P770931

CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	687.1	10.3
10°-20°	1884.6	28.1
20°-30°	2075.6	31.0
30°-40°	793.0	11.8
40°-50°	374.5	5.6
50°-60°	372.3	5.6
60°-70°	298.1	4.4
70°-80°	171.3	2.6
80°-90°	46.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4647.2	69.3
0°-40°	5440.2	81.2
0°-60°	6187.0	92.3
0°-90°	6702.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6702.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7536	
5°	7284	687
15°	6776	1885
25°	4460	2076
35°	1009	793
45°	488	374
55°	418	372
65°	303	298
75°	162	171
85°	39	47
90°	0	



TEST NUMBER: P770931

CATALOG NUMBER: LD6D70BD010-EU6DR7070959030-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7536.0
2.5°	7457.2
5°	7284.2
7.5°	7139.8
10°	7000.2
12.5°	6882.1
15°	6775.9
17.5°	6519.4
20°	6155.5
22.5°	5370.4
25°	4460.0
27.5°	3882.5
30°	3012.7
32.5°	1946.0
35°	1009.4
37.5°	545.3
40°	496.4
42.5°	492.8
45°	488.0
47.5°	477.3
50°	459.4
52.5°	439.1
55°	417.6
57.5°	393.7
60°	366.3
62.5°	335.3
65°	303.1
67.5°	267.3
70°	231.5
72.5°	195.7
75°	162.3
77.5°	127.7
80°	96.6
82.5°	68.0
85°	39.4
87.5°	15.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)