

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768409

Luminaire Tested: LD6D55D010-EU6DR6055659024-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659024-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5029.4 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768409
CATALOG NUMBER: LD6D55D010-EU6DR6055659024-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768409

CATALOG NUMBER: LD6D55D010-EU6DR6055659024-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	652614
5°	668664
10°	676750
15°	644688
20°	568423
25°	459752
30°	310980
35°	155831
40°	25274
45°	24738
50°	25242
55°	25621
60°	26332
65°	26939
70°	27569
75°	27904
80°	26930
85°	22440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 27904 cd/sqm



TEST NUMBER: P768409

CATALOG NUMBER: LD6D55D010-EU6DR6055659024-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.7	11.6
10°-20°	1576.5	31.3
20°-30°	1696.2	33.7
30°-40°	737.3	14.7
40°-50°	123.8	2.5
50°-60°	120.4	2.4
60°-70°	103.0	2.0
70°-80°	68.9	1.4
80°-90°	20.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3855.4	76.7
0°-40°	4592.6	91.3
0°-60°	4836.9	96.2
0°-90°	5029.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5029.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5973	
5°	6097	583
15°	5699	1576
25°	3814	1696
35°	1168	737
45°	160	124
55°	134	120
65°	104	103
75°	66	69
85°	18	21
90°	0	



TEST NUMBER: P768409

CATALOG NUMBER: LD6D55D010-EU6DR6055659024-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5973.0
2.5°	6141.0
5°	6096.6
7.5°	6110.6
10°	6099.8
12.5°	5973.8
15°	5699.4
17.5°	5331.0
20°	4888.7
22.5°	4415.3
25°	3813.6
27.5°	3050.3
30°	2464.9
32.5°	1899.8
35°	1168.3
37.5°	499.8
40°	177.2
42.5°	163.2
45°	160.1
47.5°	154.7
50°	148.5
52.5°	141.5
55°	134.5
57.5°	127.5
60°	120.5
62.5°	112.7
65°	104.2
67.5°	95.6
70°	86.3
72.5°	76.2
75°	66.1
77.5°	54.4
80°	42.8
82.5°	30.3
85°	17.9
87.5°	6.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)