

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768490

Luminaire Tested: LD6D55D010-EU6DR6555659027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768490
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5665.3 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768490
CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P768490
 CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	300424
5°	299666
10°	299412
15°	290179
20°	264171
25°	230211
30°	191473
35°	151715
40°	109497
45°	69174
50°	36053
55°	19163
60°	10069
65°	5542
70°	2322
75°	2550
80°	1783
85°	1541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 69174 cd/sqm



TEST NUMBER: P768490

CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.5	8.6
10°-20°	1332.1	23.5
20°-30°	1628.3	28.7
30°-40°	1321.1	23.3
40°-50°	658.3	11.6
50°-60°	183.6	3.2
60°-70°	41.7	0.7
70°-80°	10.9	0.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3446.8	60.8
0°-40°	4767.9	84.2
0°-60°	5609.9	99.0
0°-90°	5665.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5665.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5144	
5°	5111	486
15°	4799	1332
25°	3572	1628
35°	2128	1321
45°	838	658
55°	188	184
65°	40	42
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P768490

CATALOG NUMBER: LD6D55D010-EU6DR6555659027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5143.9
2.5°	5140.1
5°	5111.4
7.5°	5094.8
10°	5048.7
12.5°	4954.9
15°	4799.2
17.5°	4555.8
20°	4250.4
22.5°	3920.9
25°	3572.4
27.5°	3199.7
30°	2839.2
32.5°	2483.1
35°	2127.9
37.5°	1773.3
40°	1436.2
42.5°	1120.2
45°	837.5
47.5°	583.6
50°	396.8
52.5°	273.6
55°	188.2
57.5°	127.0
60°	86.2
62.5°	59.7
65°	40.1
67.5°	20.4
70°	13.6
72.5°	12.9
75°	11.3
77.5°	7.6
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)