

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770958

Luminaire Tested: LD6D70BD010-EU6DR7070959050-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959050-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8537.3 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770958
CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P770958

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 79 | 78 | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 83 | 78 | 75 | 81 | 77 | 74 | 79 | 76 | 73 | 71 | | |
| 5 | 89 | 80 | 74 | 69 | 88 | 79 | 73 | 69 | 78 | 72 | 68 | 76 | 71 | 68 | 74 | 70 | 67 | 65 | | |
| 6 | 84 | 75 | 68 | 63 | 83 | 74 | 68 | 63 | 72 | 67 | 63 | 71 | 66 | 62 | 69 | 65 | 62 | 60 | | |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 56 | | |
| 8 | 75 | 65 | 58 | 54 | 74 | 64 | 58 | 54 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 51 | | |
| 9 | 71 | 61 | 54 | 50 | 70 | 60 | 54 | 50 | 59 | 53 | 50 | 58 | 53 | 49 | 57 | 53 | 49 | 48 | | |
| 10 | 67 | 57 | 50 | 46 | 66 | 56 | 50 | 46 | 55 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 46 | 44 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 736243 |
| 5° | 734405 |
| 10° | 732811 |
| 15° | 732612 |
| 20° | 725450 |
| 25° | 681466 |
| 30° | 607527 |
| 35° | 484379 |
| 40° | 321630 |
| 45° | 192282 |
| 50° | 99693 |
| 55° | 52404 |
| 60° | 18531 |
| 65° | 310 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 192282 cd/sqm



TEST NUMBER: P770958

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBCSSQMB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 636.8 | 7.5 |
| 10°-20° | 1826.3 | 21.4 |
| 20°-30° | 2576.4 | 30.2 |
| 30°-40° | 2224.1 | 26.1 |
| 40°-50° | 996.0 | 11.7 |
| 50°-60° | 260.8 | 3.1 |
| 60°-70° | 17.0 | 0.2 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5039.5 | 59.0 |
| 0°-40° | 7263.6 | 85.1 |
| 0°-60° | 8520.3 | 99.8 |
| 0°-90° | 8537.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 8537.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6738 | |
| 5° | 6696 | 637 |
| 15° | 6477 | 1826 |
| 25° | 5653 | 2576 |
| 35° | 3632 | 2224 |
| 45° | 1244 | 996 |
| 55° | 275 | 261 |
| 65° | 1 | 17 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P770958

CATALOG NUMBER: LD6D70BD010-EU6DR7070959050-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 6738.4 |
| 2.5° | 6731.1 |
| 5° | 6696.0 |
| 7.5° | 6666.9 |
| 10° | 6605.1 |
| 12.5° | 6549.4 |
| 15° | 6476.7 |
| 17.5° | 6393.0 |
| 20° | 6239.2 |
| 22.5° | 5985.9 |
| 25° | 5652.7 |
| 27.5° | 5266.1 |
| 30° | 4815.4 |
| 32.5° | 4264.1 |
| 35° | 3631.5 |
| 37.5° | 2933.6 |
| 40° | 2255.0 |
| 42.5° | 1713.4 |
| 45° | 1244.4 |
| 47.5° | 857.9 |
| 50° | 586.5 |
| 52.5° | 404.7 |
| 55° | 275.1 |
| 57.5° | 166.0 |
| 60° | 84.8 |
| 62.5° | 26.7 |
| 65° | 1.2 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)