

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768503

Luminaire Tested: LD6D55D010-EU6DR6555659030-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659030-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5836.4 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768503

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P768503

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309505
5°	308724
10°	308456
15°	298947
20°	272158
25°	237164
30°	197259
35°	156299
40°	112806
45°	71263
50°	37144
55°	19744
60°	10373
65°	5707
70°	2391
75°	2640
80°	1850
85°	1541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 71263 cd/sqm



TEST NUMBER: P768503

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.1	8.6
10°-20°	1372.3	23.5
20°-30°	1677.5	28.7
30°-40°	1361.1	23.3
40°-50°	678.2	11.6
50°-60°	189.2	3.2
60°-70°	43.0	0.7
70°-80°	11.2	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3551.0	60.8
0°-40°	4912.0	84.2
0°-60°	5779.4	99.0
0°-90°	5836.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5836.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5299	
5°	5266	501
15°	4944	1372
25°	3680	1677
35°	2192	1361
45°	863	678
55°	194	189
65°	41	43
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P768503

CATALOG NUMBER: LD6D55D010-EU6DR6555659030-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5299.4
2.5°	5295.5
5°	5265.9
7.5°	5248.7
10°	5201.2
12.5°	5104.7
15°	4944.2
17.5°	4693.5
20°	4378.9
22.5°	4039.3
25°	3680.3
27.5°	3296.4
30°	2925.0
32.5°	2558.2
35°	2192.2
37.5°	1826.9
40°	1479.6
42.5°	1154.1
45°	862.8
47.5°	601.2
50°	408.8
52.5°	281.9
55°	193.9
57.5°	130.8
60°	88.8
62.5°	61.5
65°	41.3
67.5°	21.0
70°	14.0
72.5°	13.2
75°	11.7
77.5°	7.8
80°	5.5
82.5°	3.9
85°	2.3
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)