

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768539

Luminaire Tested: LD6D55D010-EU6DR6555659040-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659040-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5429.3 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768539
CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768539
 CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584053
5°	584540
10°	605112
15°	606116
20°	558028
25°	475472
30°	363994
35°	257149
40°	151787
45°	61622
50°	22335
55°	12439
60°	7146
65°	3930
70°	4121
75°	3208
80°	3335
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61622 cd/sqm



TEST NUMBER: P768539

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	514.7	9.5
10°-20°	1484.8	27.3
20°-30°	1781.4	32.8
30°-40°	1197.2	22.1
40°-50°	358.4	6.6
50°-60°	63.3	1.2
60°-70°	18.0	0.3
70°-80°	8.8	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3780.9	69.6
0°-40°	4978.1	91.7
0°-60°	5399.7	99.5
0°-90°	5429.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5429.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5346	
5°	5330	515
15°	5358	1485
25°	3944	1781
35°	1928	1197
45°	399	358
55°	65	63
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P768539

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5345.5
2.5°	5368.3
5°	5329.6
7.5°	5410.1
10°	5454.1
12.5°	5443.5
15°	5358.4
17.5°	5150.3
20°	4799.3
22.5°	4386.1
25°	3944.0
27.5°	3444.9
30°	2885.1
32.5°	2377.6
35°	1927.9
37.5°	1483.6
40°	1064.2
42.5°	695.1
45°	398.8
47.5°	211.2
50°	131.4
52.5°	91.2
55°	65.3
57.5°	47.1
60°	32.7
62.5°	21.3
65°	15.2
67.5°	13.7
70°	12.9
72.5°	9.9
75°	7.6
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)