

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771710

Luminaire Tested: LD6D75BD010-EU6DR7070959030-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771710  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR7070959030-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5319.4 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P771710  
CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771710

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	653434
5°	634016
10°	616340
15°	608254
20°	567981
25°	426696
30°	301644
35°	106853
40°	56182
45°	59845
50°	61958
55°	63128
60°	63524
65°	62177
70°	58684
75°	54373
80°	48260
85°	39113

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 63547 cd/sqm



TEST NUMBER: P771710

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	545.2	10.3
10°-20°	1495.6	28.1
20°-30°	1647.2	31.0
30°-40°	629.4	11.8
40°-50°	297.2	5.6
50°-60°	295.4	5.6
60°-70°	236.5	4.4
70°-80°	135.9	2.6
80°-90°	37.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3688.0	69.3
0°-40°	4317.3	81.2
0°-60°	4909.9	92.3
0°-90°	5319.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5319.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5980	
5°	5781	545
15°	5377	1496
25°	3539	1647
35°	801	629
45°	387	297
55°	331	295
65°	240	237
75°	129	136
85°	31	37
90°	0	



TEST NUMBER: P771710

CATALOG NUMBER: LD6D75BD010-EU6DR7070959030-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5980.5
2.5°	5918.0
5°	5780.7
7.5°	5666.1
10°	5555.3
12.5°	5461.6
15°	5377.3
17.5°	5173.7
20°	4884.9
22.5°	4261.9
25°	3539.4
27.5°	3081.1
30°	2390.9
32.5°	1544.4
35°	801.1
37.5°	432.7
40°	393.9
42.5°	391.1
45°	387.3
47.5°	378.8
50°	364.5
52.5°	348.5
55°	331.4
57.5°	312.5
60°	290.7
62.5°	266.1
65°	240.5
67.5°	212.1
70°	183.7
72.5°	155.3
75°	128.8
77.5°	101.3
80°	76.7
82.5°	54.0
85°	31.2
87.5°	12.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)