

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768801

Luminaire Tested: LD6D60D010-EU6DR3555659027-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P768801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR3555659027-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6387.9 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P768801

CATALOG NUMBER: LD6D60D010-EU6DR3555659027-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P768801

CATALOG NUMBER: LD6D60D010-EU6DR3555659027-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																																				
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																																				
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																																				
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																																				
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																																				
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																																				
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																																				
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																																				
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1920367
5°	1875243
10°	1690089
15°	1311784
20°	744018
25°	289455
30°	107983
35°	59195
40°	38695
45°	23549
50°	14992
55°	10591
60°	7758
65°	4214
70°	319
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23549 cd/sqm



TEST NUMBER: P768801

CATALOG NUMBER: LD6D60D010-EU6DR3555659027-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1572.5	24.6
10°-20°	3070.2	48.1
20°-30°	1252.1	19.6
30°-40°	299.6	4.7
40°-50°	124.9	2.0
50°-60°	51.7	0.8
60°-70°	16.2	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5894.8	92.3
0°-40°	6194.4	97.0
0°-60°	6371.0	99.7
0°-90°	6387.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6387.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	17576	
5°	17098	###
15°	11597	3070
25°	2401	1252
35°	444	300
45°	152	125
55°	56	52
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768801

CATALOG NUMBER: LD6D60D010-EU6DR3555659027-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	17576.0
2.5°	17470.5
5°	17097.7
7.5°	16353.9
10°	15233.4
12.5°	13655.7
15°	11596.9
17.5°	9078.9
20°	6398.9
22.5°	4080.3
25°	2401.0
27.5°	1357.2
30°	855.9
32.5°	601.0
35°	443.8
37.5°	343.1
40°	271.3
42.5°	209.0
45°	152.4
47.5°	114.1
50°	88.2
52.5°	70.0
55°	55.6
57.5°	45.0
60°	35.5
62.5°	25.9
65°	16.3
67.5°	5.8
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)