

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771635

Luminaire Tested: LD6D75BD010-EU6DR6570959035-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959035-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7586.2 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771635
CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P771635

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402292
5°	401278
10°	400936
15°	388573
20°	353751
25°	308269
30°	256396
35°	203156
40°	146626
45°	92631
50°	48283
55°	25660
60°	13480
65°	7407
70°	3108
75°	3430
80°	2388
85°	2010

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 92631 cd/sqm



TEST NUMBER: P771635

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	651.4	8.6
10°-20°	1783.8	23.5
20°-30°	2180.4	28.7
30°-40°	1769.1	23.3
40°-50°	881.6	11.6
50°-60°	245.9	3.2
60°-70°	55.9	0.7
70°-80°	14.5	0.2
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4615.6	60.8
0°-40°	6384.7	84.2
0°-60°	7512.1	99.0
0°-90°	7586.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7586.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6888	
5°	6845	651
15°	6426	1784
25°	4784	2180
35°	2849	1769
45°	1122	882
55°	252	246
65°	54	56
75°	15	15
85°	3	4
90°	0	



TEST NUMBER: P771635

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6888.1
2.5°	6883.1
5°	6844.6
7.5°	6822.3
10°	6760.6
12.5°	6635.1
15°	6426.5
17.5°	6100.6
20°	5691.7
22.5°	5250.4
25°	4783.7
27.5°	4284.7
30°	3801.9
32.5°	3325.1
35°	2849.4
37.5°	2374.7
40°	1923.2
42.5°	1500.1
45°	1121.5
47.5°	781.4
50°	531.4
52.5°	366.4
55°	252.0
57.5°	170.1
60°	115.4
62.5°	80.0
65°	53.6
67.5°	27.3
70°	18.2
72.5°	17.2
75°	15.2
77.5°	10.1
80°	7.1
82.5°	5.1
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)