

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771646

Luminaire Tested: LD6D75BD010-EU6DR6570959035-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771646  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959035-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6796.1 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P771646  
CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P771646

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	731086
5°	731685
10°	757452
15°	758708
20°	698509
25°	595172
30°	455627
35°	321893
40°	190011
45°	77135
50°	27962
55°	15582
60°	8938
65°	4912
70°	5175
75°	4010
80°	4216
85°	3636

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 77135 cd/sqm



TEST NUMBER: P771646

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	644.3	9.5
10°-20°	1858.5	27.3
20°-30°	2229.9	32.8
30°-40°	1498.6	22.1
40°-50°	448.6	6.6
50°-60°	79.2	1.2
60°-70°	22.5	0.3
70°-80°	11.1	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4732.7	69.6
0°-40°	6231.3	91.7
0°-60°	6759.0	99.5
0°-90°	6796.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6796.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6691	
5°	6671	644
15°	6707	1859
25°	4937	2230
35°	2413	1499
45°	499	449
55°	82	79
65°	19	23
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P771646

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6691.2
2.5°	6719.7
5°	6671.2
7.5°	6772.0
10°	6827.2
12.5°	6813.8
15°	6707.4
17.5°	6446.8
20°	6007.5
22.5°	5490.3
25°	4936.9
27.5°	4312.1
30°	3611.4
32.5°	2976.2
35°	2413.3
37.5°	1857.0
40°	1332.2
42.5°	870.0
45°	499.2
47.5°	264.3
50°	164.5
52.5°	114.1
55°	81.8
57.5°	59.0
60°	40.9
62.5°	26.6
65°	19.0
67.5°	17.1
70°	16.2
72.5°	12.4
75°	9.5
77.5°	8.6
80°	6.7
82.5°	4.8
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)