

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769295

Luminaire Tested: LD6D60D010-EU6DR6555659035-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659035-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6366.7 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769295
CATALOG NUMBER: LD6D60D010-EU6DR6555659035-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P769295

CATALOG NUMBER: LD6D60D010-EU6DR6555659035-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	337627
5°	336777
10°	336484
15°	326113
20°	296888
25°	258720
30°	215178
35°	170502
40°	123060
45°	77747
50°	40524
55°	21536
60°	11307
65°	6219
70°	2613
75°	2866
80°	1984
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 77747 cd/sqm



TEST NUMBER: P769295

CATALOG NUMBER: LD6D60D010-EU6DR6555659035-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.7	8.6
10°-20°	1497.0	23.5
20°-30°	1829.9	28.7
30°-40°	1484.7	23.3
40°-50°	739.9	11.6
50°-60°	206.3	3.2
60°-70°	46.9	0.7
70°-80°	12.2	0.2
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3873.6	60.8
0°-40°	5358.4	84.2
0°-60°	6304.6	99.0
0°-90°	6366.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6366.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5781	
5°	5744	547
15°	5394	1497
25°	4015	1830
35°	2391	1485
45°	941	740
55°	212	206
65°	45	47
75°	13	12
85°	2	3
90°	0	



TEST NUMBER: P769295

CATALOG NUMBER: LD6D60D010-EU6DR6555659035-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5780.9
2.5°	5776.6
5°	5744.4
7.5°	5725.7
10°	5673.8
12.5°	5568.5
15°	5393.5
17.5°	5120.0
20°	4776.8
22.5°	4406.4
25°	4014.8
27.5°	3596.0
30°	3190.7
32.5°	2790.6
35°	2391.4
37.5°	1992.9
40°	1614.1
42.5°	1259.0
45°	941.3
47.5°	655.8
50°	446.0
52.5°	307.5
55°	211.5
57.5°	142.7
60°	96.8
62.5°	67.1
65°	45.0
67.5°	22.9
70°	15.3
72.5°	14.4
75°	12.7
77.5°	8.5
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)