

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771191

Luminaire Tested: LD6D75BD010-EU6DR3570959040-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR3570959040-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7887.7 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771191
CATALOG NUMBER: LD6D75BD010-EU6DR3570959040-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P771191

CATALOG NUMBER: LD6D75BD010-EU6DR3570959040-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 98 | 96 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 106 | 101 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 95 | 92 | 95 | 93 | 91 | 93 | 91 | 89 | 88 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 103 | 97 | 92 | 89 | 101 | 96 | 92 | 89 | 94 | 90 | 88 | 92 | 89 | 87 | 90 | 88 | 86 | 84 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 99 | 93 | 88 | 85 | 98 | 92 | 87 | 84 | 90 | 86 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 81 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 96 | 89 | 84 | 81 | 94 | 88 | 84 | 81 | 87 | 83 | 80 | 85 | 82 | 80 | 84 | 81 | 79 | 78 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 93 | 85 | 81 | 78 | 91 | 85 | 80 | 77 | 84 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 76 | 75 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 90 | 82 | 78 | 74 | 88 | 82 | 77 | 74 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 87 | 79 | 75 | 72 | 86 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 84 | 77 | 72 | 69 | 83 | 76 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 69 | 74 | 71 | 69 | 68 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2371286 |
| 5° | 2315568 |
| 10° | 2086944 |
| 15° | 1619796 |
| 20° | 918730 |
| 25° | 357424 |
| 30° | 133342 |
| 35° | 73094 |
| 40° | 47767 |
| 45° | 29080 |
| 50° | 18511 |
| 55° | 13068 |
| 60° | 9571 |
| 65° | 5197 |
| 70° | 383 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29080 cd/sqm



TEST NUMBER: P771191

CATALOG NUMBER: LD6D75BD010-EU6DR3570959040-6LBSQW1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1941.7 | 24.6 |
| 10°-20° | 3791.1 | 48.1 |
| 20°-30° | 1546.1 | 19.6 |
| 30°-40° | 370.0 | 4.7 |
| 40°-50° | 154.2 | 2.0 |
| 50°-60° | 63.8 | 0.8 |
| 60°-70° | 20.0 | 0.3 |
| 70°-80° | 0.5 | 0.0 |
| 80°-90° | 0.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 7278.9 | 92.3 |
| 0°-40° | 7648.9 | 97.0 |
| 0°-60° | 7866.9 | 99.7 |
| 0°-90° | 7887.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7887.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 21703 | |
| 5° | 21112 | ### |
| 15° | 14320 | 3791 |
| 25° | 2965 | 1546 |
| 35° | 548 | 370 |
| 45° | 188 | 154 |
| 55° | 69 | 64 |
| 65° | 20 | 20 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P771191

CATALOG NUMBER: LD6D75BD010-EU6DR3570959040-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 21703.0 |
| 2.5° | 21572.8 |
| 5° | 21112.4 |
| 7.5° | 20194.0 |
| 10° | 18810.4 |
| 12.5° | 16862.2 |
| 15° | 14319.9 |
| 17.5° | 11210.7 |
| 20° | 7901.5 |
| 22.5° | 5038.4 |
| 25° | 2964.8 |
| 27.5° | 1675.9 |
| 30° | 1056.9 |
| 32.5° | 742.1 |
| 35° | 548.0 |
| 37.5° | 423.7 |
| 40° | 334.9 |
| 42.5° | 258.0 |
| 45° | 188.2 |
| 47.5° | 140.8 |
| 50° | 108.9 |
| 52.5° | 86.4 |
| 55° | 68.6 |
| 57.5° | 55.6 |
| 60° | 43.8 |
| 62.5° | 32.0 |
| 65° | 20.1 |
| 67.5° | 7.1 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 1.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)