

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769372

Luminaire Tested: LD6D60D010-EU6DR7055659035-6LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769372  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR7055659035-6LBCSSQMB  
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7183.3 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P769372  
CATALOG NUMBER: LD6D60D010-EU6DR7055659035-6LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P769372

CATALOG NUMBER: LD6D60D010-EU6DR7055659035-6LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619476
5°	617926
10°	616595
15°	616421
20°	610398
25°	573388
30°	511176
35°	407564
40°	270626
45°	161796
50°	83885
55°	44079
60°	15602
65°	259
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 161796 cd/sqm



TEST NUMBER: P769372

CATALOG NUMBER: LD6D60D010-EU6DR7055659035-6LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	535.8	7.5
10°-20°	1536.7	21.4
20°-30°	2167.8	30.2
30°-40°	1871.4	26.1
40°-50°	838.0	11.7
50°-60°	219.4	3.1
60°-70°	14.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4240.3	59.0
0°-40°	6111.6	85.1
0°-60°	7169.1	99.8
0°-90°	7183.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7183.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5670	
5°	5634	536
15°	5450	1537
25°	4756	2168
35°	3056	1871
45°	1047	838
55°	231	219
65°	1	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769372  
CATALOG NUMBER: LD6D60D010-EU6DR7055659035-6LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5669.7
2.5°	5663.6
5°	5634.0
7.5°	5609.6
10°	5557.6
12.5°	5510.7
15°	5449.5
17.5°	5379.1
20°	5249.7
22.5°	5036.6
25°	4756.2
27.5°	4431.0
30°	4051.7
32.5°	3587.8
35°	3055.6
37.5°	2468.3
40°	1897.4
42.5°	1441.6
45°	1047.1
47.5°	721.8
50°	493.5
52.5°	340.5
55°	231.4
57.5°	139.7
60°	71.4
62.5°	22.4
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)