

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769086

Luminaire Tested: LD6D60D010-EU6DR5055659050-6LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769086  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR5055659050-6LBCSSQMB  
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7640.4 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P769086  
CATALOG NUMBER: LD6D60D010-EU6DR5055659050-6LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P769086

CATALOG NUMBER: LD6D60D010-EU6DR5055659050-6LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95	95	93	91	88	86	85	85	83	82	82	80																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	88	86	85	85	83	82	80	77	76	74	72																	
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	83	82	80	77	76	74	72	72	70	69																
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	77	76	74	72	70	69	65	65	63	62																	
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76	74	72	70	69	65	65	63	62	62	60	59																
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72	70	69	66	65	63	62	62	60	59	59	57																
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	66	65	63	62	62	60	59	59	57	57	55																
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65	63	62	62	60	59	59	57	57	55	55	53																
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62	62	60	59	59	57	57	55	55	53	53	51																
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59	59	57	57	55	55	53	53	51	51	49	49																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1345055
5°	1330955
10°	1309033
15°	1191984
20°	991866
25°	704083
30°	372674
35°	151870
40°	56396
45°	25820
50°	10590
55°	5543
60°	2732
65°	801
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25820 cd/sqm



TEST NUMBER: P769086

CATALOG NUMBER: LD6D60D010-EU6DR5055659050-6LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1147.0	15.0
10°-20°	2898.8	37.9
20°-30°	2603.8	34.1
30°-40°	815.3	10.7
40°-50°	142.7	1.9
50°-60°	28.5	0.4
60°-70°	4.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6649.6	87.0
0°-40°	7464.9	97.7
0°-60°	7636.1	99.9
0°-90°	7640.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7640.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12310	
5°	12135	###
15°	10538	2899
25°	5840	2604
35°	1139	815
45°	167	143
55°	29	28
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769086  
CATALOG NUMBER: LD6D60D010-EU6DR5055659050-6LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12310.5
2.5°	12249.3
5°	12135.1
7.5°	11960.7
10°	11798.8
12.5°	11279.9
15°	10537.8
17.5°	9595.4
20°	8530.5
22.5°	7298.5
25°	5840.3
27.5°	4293.8
30°	2953.9
32.5°	1923.2
35°	1138.6
37.5°	653.9
40°	395.4
42.5°	257.4
45°	167.1
47.5°	101.7
50°	62.3
52.5°	42.6
55°	29.1
57.5°	19.7
60°	12.5
62.5°	7.3
65°	3.1
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)