

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771736

Luminaire Tested: LD6D75BD010-EU6DR7070959040-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR7070959040-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5626.7 lumens  
Efficiency: N/A  
Efficacy: 77.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P771736  
CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771736

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	691184
5°	670649
10°	651954
15°	643398
20°	600805
25°	451349
30°	319067
35°	113015
40°	59434
45°	63291
50°	65544
55°	66786
60°	67195
65°	65771
70°	62071
75°	57497
80°	51029
85°	41495

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 67208 cd/sqm



TEST NUMBER: P771736

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	576.7	10.3
10°-20°	1582.0	28.1
20°-30°	1742.3	31.0
30°-40°	665.7	11.8
40°-50°	314.3	5.6
50°-60°	312.5	5.6
60°-70°	250.2	4.4
70°-80°	143.8	2.6
80°-90°	39.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3901.1	69.3
0°-40°	4566.8	81.2
0°-60°	5193.6	92.3
0°-90°	5626.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5626.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6326	
5°	6115	577
15°	5688	1582
25°	3744	1742
35°	847	666
45°	410	314
55°	351	313
65°	254	250
75°	136	144
85°	33	39
90°	0	



TEST NUMBER: P771736

CATALOG NUMBER: LD6D75BD010-EU6DR7070959040-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6326.0
2.5°	6259.9
5°	6114.7
7.5°	5993.5
10°	5876.3
12.5°	5777.1
15°	5688.0
17.5°	5472.7
20°	5167.2
22.5°	4508.1
25°	3743.9
27.5°	3259.2
30°	2529.0
32.5°	1633.6
35°	847.3
37.5°	457.7
40°	416.7
42.5°	413.7
45°	409.6
47.5°	400.6
50°	385.6
52.5°	368.6
55°	350.6
57.5°	330.5
60°	307.5
62.5°	281.4
65°	254.4
67.5°	224.4
70°	194.3
72.5°	164.3
75°	136.2
77.5°	107.2
80°	81.1
82.5°	57.1
85°	33.1
87.5°	13.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)