

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771115

Luminaire Tested: LD6D75BD010-EU6DR3070959050-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR3070959050-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8104.8 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771115

CATALOG NUMBER: LD6D75BD010-EU6DR3070959050-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P771115

CATALOG NUMBER: LD6D75BD010-EU6DR3070959050-6LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1994790	1994790	1994790
5°	1937529	1935263	1937622
10°	1678190	1666360	1677793
15°	1094940	1089052	1083584
20°	544459	564888	543734
25°	274263	309270	268639
30°	109809	119646	95676
35°	50935	48777	40890
40°	21992	24421	20713
45°	15512	19257	15653
50°	5335	14016	5633
55°	3069	5805	3243
60°	2159	2541	2159
65°	1395	1395	1395
70°	850	582	850
75°	0	384	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 19257 cd/sqm



TEST NUMBER: P771115

CATALOG NUMBER: LD6D75BD010-EU6DR3070959050-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2291.7	28.3
10°-20°	3690.7	45.5
20°-30°	1594.9	19.7
30°-40°	363.5	4.5
40°-50°	124.8	1.5
50°-60°	30.5	0.4
60°-70°	7.9	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7577.3	93.5
0°-40°	7940.8	98.0
0°-60°	8096.1	99.9
0°-90°	8104.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8104.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	26061	26061	26061	26061	26061	
5°	25216	25192	25187	25240	25218	2294
15°	13817	13651	13743	13698	13674	3700
25°	3247	3370	3662	3284	3181	1554
35°	545	557	522	518	438	370
45°	143	178	178	178	145	102
55°	23	24	44	26	24	22
65°	8	8	8	8	8	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P771115

CATALOG NUMBER: LD6D75BD010-EU6DR3070959050-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	26060.9	26060.9	26060.9	26060.9	26060.9
2.5°	25888.2	25870.3	25880.5	25893.3	25898.4
5°	25216.5	25192.1	25187.0	25239.5	25217.7
7.5°	23861.5	23826.9	23774.5	23893.4	24004.8
10°	21591.6	21553.2	21439.4	21495.7	21586.5
12.5°	18240.6	18116.5	18113.9	18293.1	18268.7
15°	13817.4	13651.0	13743.1	13698.4	13674.1
17.5°	9291.8	9227.8	9350.6	9313.5	9153.6
20°	6684.1	6700.8	6934.9	6817.2	6675.2
22.5°	4877.5	4937.6	5215.3	4912.0	4800.7
25°	3247.4	3370.2	3661.9	3284.5	3180.8
27.5°	1997.3	2053.6	2349.2	1971.7	1915.4
30°	1242.4	1214.2	1353.7	1161.8	1082.5
32.5°	815.0	779.2	824.0	739.6	675.6
35°	545.1	556.6	522.0	518.2	437.6
37.5°	340.3	391.5	345.5	368.5	281.5
40°	220.1	284.0	244.4	270.0	207.3
42.5°	180.4	218.8	200.9	213.7	184.2
45°	143.3	177.9	177.9	177.9	144.6
47.5°	79.3	119.0	152.3	121.6	84.4
50°	44.8	60.1	117.7	62.7	47.3
52.5°	30.7	34.5	80.6	35.8	32.0
55°	23.0	24.3	43.5	25.6	24.3
57.5°	17.9	19.2	23.0	19.2	17.9
60°	14.1	14.1	16.6	15.4	14.1
62.5°	10.2	10.2	11.5	10.2	10.2
65°	7.7	7.7	7.7	7.7	7.7
67.5°	3.8	5.1	5.1	5.1	5.1
70°	3.8	2.6	2.6	2.6	3.8
72.5°	2.6	1.3	1.3	1.3	1.3
75°	0.0	0.0	1.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)