

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769409

Luminaire Tested: LD6D60D010-EU6DR7055659050-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769409  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D60D010-EU6DR7055659050-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4755.9 lumens  
Efficiency: N/A  
Efficacy: 73.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P769409

CATALOG NUMBER: LD6D60D010-EU6DR7055659050-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P769409

CATALOG NUMBER: LD6D60D010-EU6DR7055659050-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	584228
5°	566860
10°	551059
15°	543835
20°	507822
25°	381499
30°	269687
35°	95529
40°	50234
45°	53510
50°	55396
55°	56442
60°	56794
65°	55585
70°	52455
75°	48590
80°	43164
85°	34976

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 56816 cd/sqm



TEST NUMBER: P769409

CATALOG NUMBER: LD6D60D010-EU6DR7055659050-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	487.5	10.3
10°-20°	1337.2	28.1
20°-30°	1472.7	31.0
30°-40°	562.7	11.8
40°-50°	265.7	5.6
50°-60°	264.1	5.6
60°-70°	211.5	4.4
70°-80°	121.5	2.6
80°-90°	33.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3297.4	69.3
0°-40°	3860.1	81.2
0°-60°	4389.9	92.3
0°-90°	4755.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4755.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5347	
5°	5168	487
15°	4808	1337
25°	3164	1473
35°	716	563
45°	346	266
55°	296	264
65°	215	211
75°	115	122
85°	28	33
90°	0	



TEST NUMBER: P769409

CATALOG NUMBER: LD6D60D010-EU6DR7055659050-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5347.1
2.5°	5291.2
5°	5168.4
7.5°	5066.0
10°	4966.9
12.5°	4883.1
15°	4807.8
17.5°	4625.8
20°	4367.5
22.5°	3810.5
25°	3164.5
27.5°	2754.8
30°	2137.6
32.5°	1380.8
35°	716.2
37.5°	386.9
40°	352.2
42.5°	349.6
45°	346.3
47.5°	338.6
50°	325.9
52.5°	311.5
55°	296.3
57.5°	279.4
60°	259.9
62.5°	237.9
65°	215.0
67.5°	189.6
70°	164.2
72.5°	138.8
75°	115.1
77.5°	90.6
80°	68.6
82.5°	48.3
85°	27.9
87.5°	11.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)