

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771593

Luminaire Tested: LD6D75BD010-EU6DR6070959050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6070959050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7273.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771593
CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P771593

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	943751
5°	966966
10°	978646
15°	932294
20°	821991
25°	664854
30°	449710
35°	225350
40°	36556
45°	35786
50°	36495
55°	37050
60°	38066
65°	38935
70°	39868
75°	40315
80°	38885
85°	32469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 40315 cd/sqm



TEST NUMBER: P771593

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	842.6	11.6
10°-20°	2279.8	31.3
20°-30°	2452.8	33.7
30°-40°	1066.2	14.7
40°-50°	179.1	2.5
50°-60°	174.1	2.4
60°-70°	148.9	2.0
70°-80°	99.7	1.4
80°-90°	29.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5575.2	76.7
0°-40°	6641.4	91.3
0°-60°	6994.7	96.2
0°-90°	7273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8638	
5°	8816	843
15°	8242	2280
25°	5515	2453
35°	1690	1066
45°	232	179
55°	194	174
65°	151	149
75°	96	100
85°	26	30
90°	0	



TEST NUMBER: P771593

CATALOG NUMBER: LD6D75BD010-EU6DR6070959050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8637.6
2.5°	8880.5
5°	8816.4
7.5°	8836.6
10°	8820.9
12.5°	8638.8
15°	8242.0
17.5°	7709.1
20°	7069.5
22.5°	6384.9
25°	5514.9
27.5°	4411.0
30°	3564.5
32.5°	2747.3
35°	1689.5
37.5°	722.8
40°	256.3
42.5°	236.1
45°	231.6
47.5°	223.7
50°	214.7
52.5°	204.6
55°	194.5
57.5°	184.4
60°	174.2
62.5°	163.0
65°	150.6
67.5°	138.3
70°	124.8
72.5°	110.2
75°	95.5
77.5°	78.7
80°	61.8
82.5°	43.8
85°	25.9
87.5°	9.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)