

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769829

Luminaire Tested: LD6D65D010-EU6DR5055659030-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR5055659030-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7973.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769829

CATALOG NUMBER: LD6D65D010-EU6DR5055659030-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P769829

CATALOG NUMBER: LD6D65D010-EU6DR5055659030-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95				95															
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90															
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85															
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80				80															
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76				76															
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72				72															
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69															
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65				65															
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62				62															
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59				59															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1403618
5°	1388909
10°	1366026
15°	1243881
20°	1035049
25°	734728
30°	388899
35°	158472
40°	58863
45°	26948
50°	11049
55°	5772
60°	2841
65°	827
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26948 cd/sqm



TEST NUMBER: P769829

CATALOG NUMBER: LD6D65D010-EU6DR5055659030-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1196.9	15.0
10°-20°	3025.0	37.9
20°-30°	2717.2	34.1
30°-40°	850.7	10.7
40°-50°	149.0	1.9
50°-60°	29.7	0.4
60°-70°	4.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6939.1	87.0
0°-40°	7789.8	97.7
0°-60°	7968.5	99.9
0°-90°	7973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7973.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12846	
5°	12664	###
15°	10997	3025
25°	6094	2717
35°	1188	851
45°	174	149
55°	30	30
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769829

CATALOG NUMBER: LD6D65D010-EU6DR5055659030-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	12846.5
2.5°	12782.6
5°	12663.5
7.5°	12481.5
10°	12312.5
12.5°	11771.0
15°	10996.6
17.5°	10013.1
20°	8901.9
22.5°	7616.3
25°	6094.5
27.5°	4480.7
30°	3082.5
32.5°	2007.0
35°	1188.1
37.5°	682.3
40°	412.7
42.5°	268.6
45°	174.4
47.5°	106.1
50°	65.0
52.5°	44.4
55°	30.3
57.5°	20.6
60°	13.0
62.5°	7.6
65°	3.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)