

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772399

Luminaire Tested: LD6D80BD010-EU6DR6570959027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P772399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6290.8 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772399
CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P772399

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	676739
5°	677295
10°	701136
15°	702297
20°	646582
25°	550928
30°	421752
35°	297964
40°	175877
45°	71403
50°	25888
55°	14420
60°	8260
65°	4550
70°	4792
75°	3715
80°	3901
85°	3259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 71403 cd/sqm



TEST NUMBER: P772399

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	596.4	9.5
10°-20°	1720.4	27.3
20°-30°	2064.1	32.8
30°-40°	1387.1	22.1
40°-50°	415.3	6.6
50°-60°	73.3	1.2
60°-70°	20.8	0.3
70°-80°	10.2	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4380.9	69.6
0°-40°	5768.0	91.7
0°-60°	6256.6	99.5
0°-90°	6290.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6290.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6194	
5°	6175	596
15°	6209	1720
25°	4570	2064
35°	2234	1387
45°	462	415
55°	76	73
65°	18	21
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P772399

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6193.8
2.5°	6220.2
5°	6175.3
7.5°	6268.6
10°	6319.6
12.5°	6307.3
15°	6208.7
17.5°	5967.6
20°	5560.9
22.5°	5082.1
25°	4569.9
27.5°	3991.6
30°	3342.9
32.5°	2754.9
35°	2233.9
37.5°	1719.0
40°	1233.1
42.5°	805.4
45°	462.1
47.5°	244.7
50°	152.3
52.5°	105.6
55°	75.7
57.5°	54.6
60°	37.8
62.5°	24.6
65°	17.6
67.5°	15.8
70°	15.0
72.5°	11.4
75°	8.8
77.5°	7.9
80°	6.2
82.5°	4.4
85°	2.6
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)