

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770085

Luminaire Tested: LD6D65D010-EU6DR6555659035-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659035-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5365.8 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770085

CATALOG NUMBER: LD6D65D010-EU6DR6555659035-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P770085

CATALOG NUMBER: LD6D65D010-EU6DR6555659035-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	577214
5°	577686
10°	598034
15°	599023
20°	551494
25°	469903
30°	359730
35°	254147
40°	150018
45°	60896
50°	22080
55°	12306
60°	7058
65°	3878
70°	4089
75°	3166
80°	3335
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 60896 cd/sqm



TEST NUMBER: P770085

CATALOG NUMBER: LD6D65D010-EU6DR6555659035-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.7	9.5
10°-20°	1467.4	27.3
20°-30°	1760.6	32.8
30°-40°	1183.2	22.1
40°-50°	354.2	6.6
50°-60°	62.5	1.2
60°-70°	17.8	0.3
70°-80°	8.7	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3736.6	69.6
0°-40°	4919.8	91.7
0°-60°	5336.5	99.5
0°-90°	5365.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5365.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5283	
5°	5267	509
15°	5296	1467
25°	3898	1761
35°	1905	1183
45°	394	354
55°	65	63
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P770085

CATALOG NUMBER: LD6D65D010-EU6DR6555659035-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5282.9
2.5°	5305.4
5°	5267.1
7.5°	5346.7
10°	5390.3
12.5°	5379.8
15°	5295.7
17.5°	5090.0
20°	4743.1
22.5°	4334.7
25°	3897.8
27.5°	3404.6
30°	2851.3
32.5°	2349.8
35°	1905.4
37.5°	1466.2
40°	1051.8
42.5°	686.9
45°	394.1
47.5°	208.7
50°	129.9
52.5°	90.1
55°	64.6
57.5°	46.5
60°	32.3
62.5°	21.0
65°	15.0
67.5°	13.5
70°	12.8
72.5°	9.8
75°	7.5
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)