

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770904

Luminaire Tested: LD6D70BD010-EU6DR7070959024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4312.6 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770904
CATALOG NUMBER: LD6D70BD010-EU6DR7070959024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P770904

CATALOG NUMBER: LD6D70BD010-EU6DR7070959024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	529762
5°	514017
10°	499691
15°	493136
20°	460487
25°	345935
30°	244555
35°	86619
40°	45542
45°	48519
50°	50246
55°	51185
60°	51506
65°	50414
70°	47567
75°	44073
80°	39137
85°	31717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 51509 cd/sqm



TEST NUMBER: P770904

CATALOG NUMBER: LD6D70BD010-EU6DR7070959024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	442.0	10.3
10°-20°	1212.5	28.1
20°-30°	1335.4	31.0
30°-40°	510.2	11.8
40°-50°	240.9	5.6
50°-60°	239.5	5.6
60°-70°	191.8	4.4
70°-80°	110.2	2.6
80°-90°	30.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2990.0	69.3
0°-40°	3500.2	81.2
0°-60°	3980.6	92.3
0°-90°	4312.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4312.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4849	
5°	4687	442
15°	4360	1213
25°	2870	1335
35°	649	510
45°	314	241
55°	269	240
65°	195	192
75°	104	110
85°	25	30
90°	0	



TEST NUMBER: P770904

CATALOG NUMBER: LD6D70BD010-EU6DR7070959024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4848.6
2.5°	4797.9
5°	4686.6
7.5°	4593.7
10°	4503.9
12.5°	4427.9
15°	4359.6
17.5°	4194.5
20°	3960.4
22.5°	3455.3
25°	2869.5
27.5°	2498.0
30°	1938.4
32.5°	1252.1
35°	649.4
37.5°	350.8
40°	319.3
42.5°	317.0
45°	314.0
47.5°	307.1
50°	295.6
52.5°	282.5
55°	268.7
57.5°	253.3
60°	235.7
62.5°	215.7
65°	195.0
67.5°	172.0
70°	148.9
72.5°	125.9
75°	104.4
77.5°	82.1
80°	62.2
82.5°	43.8
85°	25.3
87.5°	10.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)