

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772361

Luminaire Tested: LD6D80BD010-EU6DR6070959040-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P772361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6070959040-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9216.1 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772361

CATALOG NUMBER: LD6D80BD010-EU6DR6070959040-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P772361

CATALOG NUMBER: LD6D80BD010-EU6DR6070959040-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1195892
5°	1225302
10°	1240102
15°	1181362
20°	1041596
25°	842469
30°	569868
35°	285559
40°	46326
45°	45336
50°	46251
55°	46937
60°	48250
65°	49354
70°	50506
75°	51123
80°	49267
85°	41119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 51123 cd/sqm



TEST NUMBER: P772361

CATALOG NUMBER: LD6D80BD010-EU6DR6070959040-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1067.7	11.6
10°-20°	2888.8	31.3
20°-30°	3108.2	33.7
30°-40°	1351.1	14.7
40°-50°	226.9	2.5
50°-60°	220.6	2.4
60°-70°	188.7	2.0
70°-80°	126.3	1.4
80°-90°	37.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7064.7	76.7
0°-40°	8415.8	91.3
0°-60°	8863.3	96.2
0°-90°	9216.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9216.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10945	
5°	11172	###
15°	10444	2889
25°	6988	3108
35°	2141	1351
45°	293	227
55°	246	221
65°	191	189
75°	121	126
85°	33	38
90°	0	



TEST NUMBER: P772361

CATALOG NUMBER: LD6D80BD010-EU6DR6070959040-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10945.3
2.5°	11253.0
5°	11171.8
7.5°	11197.4
10°	11177.5
12.5°	10946.7
15°	10443.9
17.5°	9768.7
20°	8958.2
22.5°	8090.8
25°	6988.2
27.5°	5589.5
30°	4516.9
32.5°	3481.3
35°	2140.9
37.5°	915.9
40°	324.8
42.5°	299.1
45°	293.4
47.5°	283.5
50°	272.1
52.5°	259.2
55°	246.4
57.5°	233.6
60°	220.8
62.5°	206.5
65°	190.9
67.5°	175.2
70°	158.1
72.5°	139.6
75°	121.1
77.5°	99.7
80°	78.3
82.5°	55.6
85°	32.8
87.5°	11.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)