

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772427

Luminaire Tested: LD6D80BD010-EU6DR6570959040-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959040-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8996.5 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772427

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P772427

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	477078
5°	475875
10°	475471
15°	460809
20°	419514
25°	365577
30°	304055
35°	240923
40°	173882
45°	109852
50°	57260
55°	30435
60°	15979
65°	8789
70°	3688
75°	4062
80°	2825
85°	2412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 109852 cd/sqm



TEST NUMBER: P772427

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	772.5	8.6
10°-20°	2115.4	23.5
20°-30°	2585.7	28.7
30°-40°	2098.0	23.3
40°-50°	1045.5	11.6
50°-60°	291.6	3.2
60°-70°	66.2	0.7
70°-80°	17.2	0.2
80°-90°	4.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5473.6	60.8
0°-40°	7571.6	84.2
0°-60°	8908.6	99.0
0°-90°	8996.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8996.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8169	
5°	8117	772
15°	7621	2115
25°	5673	2586
35°	3379	2098
45°	1330	1045
55°	299	292
65°	64	66
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P772427

CATALOG NUMBER: LD6D80BD010-EU6DR6570959040-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8168.6
2.5°	8162.6
5°	8117.0
7.5°	8090.6
10°	8017.4
12.5°	7868.5
15°	7621.2
17.5°	7234.7
20°	6749.8
22.5°	6226.4
25°	5673.0
27.5°	5081.2
30°	4508.6
32.5°	3943.3
35°	3379.1
37.5°	2816.1
40°	2280.7
42.5°	1779.0
45°	1330.0
47.5°	926.7
50°	630.2
52.5°	434.5
55°	298.9
57.5°	201.7
60°	136.8
62.5°	94.8
65°	63.6
67.5°	32.4
70°	21.6
72.5°	20.4
75°	18.0
77.5°	12.0
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)