

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773102

Luminaire Tested: LD6D85BD010-EU6DR6070959027-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6070959027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9003.3 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773102
CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773102

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1168271
5°	1196994
10°	1211456
15°	1154079
20°	1017539
25°	823011
30°	556696
35°	278970
40°	45256
45°	44300
50°	45181
55°	45851
60°	47135
65°	48216
70°	49356
75°	49940
80°	48134
85°	40116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 49940 cd/sqm



TEST NUMBER: P773102

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1043.1	11.6
10°-20°	2822.1	31.3
20°-30°	3036.4	33.7
30°-40°	1319.9	14.7
40°-50°	221.7	2.5
50°-60°	215.6	2.4
60°-70°	184.4	2.0
70°-80°	123.4	1.4
80°-90°	36.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6901.6	76.7
0°-40°	8221.4	91.3
0°-60°	8658.6	96.2
0°-90°	9003.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9003.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10692	
5°	10914	###
15°	10203	2822
25°	6827	3036
35°	2092	1320
45°	287	222
55°	241	216
65°	186	184
75°	118	123
85°	32	37
90°	0	



TEST NUMBER: P773102

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10692.5
2.5°	10993.1
5°	10913.7
7.5°	10938.8
10°	10919.3
12.5°	10693.9
15°	10202.7
17.5°	9543.1
20°	8751.3
22.5°	7903.9
25°	6826.8
27.5°	5460.3
30°	4412.5
32.5°	3400.9
35°	2091.5
37.5°	894.8
40°	317.3
42.5°	292.2
45°	286.7
47.5°	276.9
50°	265.8
52.5°	253.3
55°	240.7
57.5°	228.2
60°	215.7
62.5°	201.8
65°	186.5
67.5°	171.2
70°	154.5
72.5°	136.4
75°	118.3
77.5°	97.4
80°	76.5
82.5°	54.3
85°	32.0
87.5°	11.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)