

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773260

Luminaire Tested: LD6D85BD010-EU6DR7070959030-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773260  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D85BD010-EU6DR7070959030-6LBCSSQMMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10215.6 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P773260  
CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P773260

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																											
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																											
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																											
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71																											
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65																											
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60																											
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56																											
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51																											
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48																											
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	880969
5°	878774
10°	876864
15°	876619
20°	868047
25°	815428
30°	726954
35°	579601
40°	384858
45°	230093
50°	119292
55°	62690
60°	22180
65°	362
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 230093 cd/sqm



TEST NUMBER: P773260

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	762.0	7.5
10°-20°	2185.3	21.4
20°-30°	3082.9	30.2
30°-40°	2661.3	26.1
40°-50°	1191.8	11.7
50°-60°	312.0	3.1
60°-70°	20.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6030.1	59.0
0°-40°	8691.5	85.1
0°-60°	10195.3	99.8
0°-90°	10215.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10215.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8063	
5°	8012	762
15°	7750	2185
25°	6764	3083
35°	4345	2661
45°	1489	1192
55°	329	312
65°	1	20
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P773260

CATALOG NUMBER: LD6D85BD010-EU6DR7070959030-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8063.0
2.5°	8054.3
5°	8012.3
7.5°	7977.5
10°	7903.5
12.5°	7836.8
15°	7749.8
17.5°	7649.8
20°	7465.6
22.5°	7162.6
25°	6763.9
27.5°	6301.4
30°	5762.0
32.5°	5102.3
35°	4345.4
37.5°	3510.3
40°	2698.3
42.5°	2050.2
45°	1489.1
47.5°	1026.5
50°	701.8
52.5°	484.3
55°	329.1
57.5°	198.6
60°	101.5
62.5°	31.9
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)