

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770957

Luminaire Tested: LD6D70BD010-EU6DR7070959040-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR7070959040-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7090.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770957

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770957
 CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	870961
5°	845081
10°	821524
15°	810741
20°	757064
25°	568747
30°	402058
35°	142413
40°	74881
45°	79762
50°	82593
55°	84140
60°	84677
65°	82886
70°	78203
75°	72441
80°	64305
85°	52151

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 84696 cd/sqm



TEST NUMBER: P770957

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	726.7	10.3
10°-20°	1993.5	28.1
20°-30°	2195.5	31.0
30°-40°	838.8	11.8
40°-50°	396.1	5.6
50°-60°	393.8	5.6
60°-70°	315.3	4.4
70°-80°	181.2	2.6
80°-90°	49.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4915.7	69.3
0°-40°	5754.6	81.2
0°-60°	6544.4	92.3
0°-90°	7090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7090.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7971	
5°	7705	727
15°	7167	1993
25°	4718	2196
35°	1068	839
45°	516	396
55°	442	394
65°	321	315
75°	172	181
85°	42	49
90°	0	



TEST NUMBER: P770957

CATALOG NUMBER: LD6D70BD010-EU6DR7070959040-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7971.4
2.5°	7888.1
5°	7705.1
7.5°	7552.3
10°	7404.7
12.5°	7279.7
15°	7167.4
17.5°	6896.1
20°	6511.1
22.5°	5680.7
25°	4717.7
27.5°	4106.8
30°	3186.8
32.5°	2058.5
35°	1067.7
37.5°	576.8
40°	525.0
42.5°	521.2
45°	516.2
47.5°	504.8
50°	485.9
52.5°	464.4
55°	441.7
57.5°	416.5
60°	387.5
62.5°	354.6
65°	320.6
67.5°	282.7
70°	244.8
72.5°	207.0
75°	171.6
77.5°	135.0
80°	102.2
82.5°	71.9
85°	41.6
87.5°	16.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)